

## Features

- IEC-584-3
- Fast response, welded exposed junction
- Miniature Plug termination
- Unique single shot cable construction Resistant to chemicals, oils and fluids. Suitable for aerospace applications and is widely used in autoclaves.

## RS PRO PTFE Single Shot IEC Exposed Junction Thermocouple with Miniature Plug - Type T

RS Stock No.: 0652764



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Unique single shot cable construction Resistant to chemicals, oils and fluids. Suitable for aerospace applications and is widely used in autoclaves.

## General Specifications

Thermocouple Type	Type T
Temperature Measurement Range	+250°C
Construction	Terminated with a miniature flat pin plug
Measuring Junction	Exposed
Standards Met	IEC
Application	Fast response, welded exposed junction

## Mechanical Specifications

Termination	Miniature Plug
Length	0.3m (0.98ft)
Cable Insulation	1/0.376mm PTFE Flat Pair

## Approvals

Declarations	RoHS
--------------	------

## Similar Products

Colour Code	Type	Style	Cable Size	Length	Termination	RS Stock#
IEC	K	PTFE	1/0.376mm	0.3m (0.98ft)	Miniature Plug	0652763
IEC	K	PTFE	1/0.376mm	1m (3.3ft)	Miniature Plug	8722635
IEC	K	PTFE	1/0.376mm	2m (6.56ft)	Miniature Plug	8722638
IEC	K	PTFE	1/0.376mm	3m (9.84ft)	Miniature Plug	2209509
IEC	K	PTFE	1/0.376mm	5m (16.4 ft)	Miniature Plug	8722632
IEC	K	PTFE	1/0.376mm	10m (32.8ft)	Miniature Plug	8722641
IEC	T	PTFE	1/0.376mm	0.3m (0.98ft)	Miniature Plug	0652764
IEC	T	PTFE	1/0.376mm	1m (3.3ft)	Miniature Plug	8722644
IEC	T	PTFE	1/0.376mm	2m (6.56ft)	Miniature Plug	8722648
IEC	T	PTFE	1/0.376mm	3m (9.84ft)	Miniature Plug	2209510
IEC	T	PTFE	1/0.376mm	5m (16.4 ft)	Miniature Plug	8722657
IEC	T	PTFE	1/0.376mm	10m (32.8ft)	Miniature Plug	8722650