

1/4" -1/2" SOCKET SET 82 PIECES

RSL.151-EPW82PB



INCLUDING :

- 1 x 1/4" ratchet : RL.151.
- 13 x 1/4" 6-point sockets - metric : R.HT. 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm
- 2 x 1/4" extension - L 55mm : R.209ST - L 100mm : R.210ST
- 1 X 1/4" flexible extension L 150 mm : R.208ST
- 1 x 1/4" Universal joint : R.240AT.
- 1 x 1/4" socket nut handle : R.236BT.
- 1 x 1/4" sliding bar handle : R.120AT.
- 1 x 1/4" adaptator to 1/4" bit : R.230T.
- 6 x 1/4" Torx bit sockets : R.XT 8 - 10 - 15 - 20 - 25 - 30 mm.
- 4 x 1/4" hexagonal bit sockets : RT.T 3 - 4 - 5 - 6 mm.
- 3 x 1/4" slotted bit sockets : RS.T 4 - 5,5 - 7 mm.
- 2 x 1/4" Pozidriv® bit sockets : RD.T 1T - 2T . PZ1 - PZ2.
- 2 x 1/4" Phillips® bit sockets : RP.T 1T - 2T / PH1 - PH2.
- 1/4" bits. 7PC PZ-3,4,PH-3,4,FD-4,5,5,5,6,5
- 1/4" bits. 8PC HW-6,7,8,10, TX-20,25,40,45.
- 1 x 1/2" ratchet 72T : SL.151.
- 12 x 1/2" metric 6-point sockets : S.HT 14 - 15 - 16 - 17 - 18 - 19 - 20 - 22 - 24 - 27 - 30 - 32 mm.
- 1 x 1/2" universal joint : S.240AT.
- 2 x 1/2" extension - L 130 mm : S.210ST - L 250mm : S.215ST.
- 1 X 1/2" to 3/8" coupler : S.230TW
- 1 X 3/8" to 1/2" coupler 3 way : J.235TW
- 2 x 1/2" spark plug socket : 16 mm B.S16A1T - 21 mm B.S21A2T
- 9 x slim combination wrenches : 40B. 8 - 10 - 11 - 12 - 13 - 14 - 17 - 19 - 22 mm
- 1 x blow mold case size L :

Closed has the same dimensions of 1 1/2 module, open takes up the space of 1 drawer (3 modules)



SKU	SKU Desc	EAN Code	RRP
RSL.151-EPW82PB	FACOM 1/4 1/2 SOCKET WRENCHES SET 82PC	3662424112614	€xx.xx