

PATG 3/30 - Conductor marker carrier



0822466

<https://www.phoenixcontact.com/gb/products/0822466>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, transparent, unlabeled, cable diameter range: 4 ... 7 mm, mounting type: slide-on, text field height: 4 mm, text field width: 30 mm

Your advantages

- The corresponding UC-WMT ..., US-WMT ..., and EMT ... insert labels are used for marking
- These conductor marking systems consist of marker carriers and insert labels
- The PATG ... collar is a captive marker carrier
- Can be used to mark conductors with a diameter of 0.6 mm ... 50 mm

Commercial data

Item number	0822466
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	BG221A
Product key	BG221A
Catalog page	Page 248 (C-3-2019)
GTIN	4046356326193
Weight per piece (including packing)	0.82 g
Weight per piece (excluding packing)	0.796 g
Customs tariff number	39269097
Country of origin	DE

PATG 3/30 - Conductor marker carrier



0822466

<https://www.phoenixcontact.com/gb/products/0822466>

Technical data

Product properties

Product type	Marker carrier cable
Type	Profile

Dimensions

Width	30 mm
Height	7.5 mm
Depth	9.41 mm

External dimensions

Outside diameter	4 mm ... 7 mm
------------------	---------------

Text field

Text field width	30 mm
Text field height	4 mm

Material specifications

RoHS compliant	yes
Color	transparent
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Cable/line

External cable diameter	4 mm ... 7 mm
-------------------------	---------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	slide-on
---------------	----------

PATG 3/30 - Conductor marker carrier



0822466

<https://www.phoenixcontact.com/gb/products/0822466>

Classifications

ECLASS

ECLASS-13.0	27281105
-------------	----------

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PATG 3/30 - Conductor marker carrier



0822466

<https://www.phoenixcontact.com/gb/products/0822466>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk