

## M3R



LED LENSER M3R

### 8303 M3R Black in Gift Box

Ultra-portable and ultra-bright, LED Lenser's smallest-ever rechargeable hand torch weighs just 45 grams yet blasts out an almighty 220 lumens. At barely four inches in length it will easily clip into a shirt pocket or overalls and it can be recharged by mains or USB, making it a great choice for travel and jobs on the go. It combines patented Advanced Focus System optics and micro-controlled Smart Light Technology for a high quality near-to-far beam and a choice of three useful light modes – Power, Low Power and Defence Strobe. A simple push-button Dynamic Switch at one end and single-handed Speed Focus at the other mean that selection of any light or focus setting is both simple and fast. Like all LED Lenser torches it is built to last, with an anodised metal casing containing hard gold-plated battery contacts inside for optimum durability and power transmission. A generous burn time of up to 6 hours covers most tasks in a day's work but just to keep it running smoothly there's a helpful Low Battery Message System to tell you when the batteries do need to be re-charged. Supplied with wrist strap, belt pouch, clip, charger and one Lithium-ion rechargeable battery.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability second to none.

- LED Lenser's smallest rechargeable hand torch
- Energy efficient CREE Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot or flawless flood illumination
- Smart Light Technology™. Micro-chip controlled light options -Power, Low Power, Defence Strobe
- Dynamic Switch™ - Reactive, single switch control
- Speed Focus™ enables smooth single-handed beam focusing
- Robust, yet lightweight aircraft-grade aluminium housing
- Low Battery Message System
- Charging station with USB connection
- Charging status light
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant (IPX54)

Lumens	Burn Time	Dimensions	Weight	Power Supply
220	up to 6 hours	100mm x 20mm	45 grams	ICR10440 Lithium rechargeable battery

