












ACCESSORIES / REPLACEMENT PARTS

POWER AND ENERGY QUALITY ANALYSERS AND LOGGERS

C.A 8220, C.A 8331, C.A 8333, C.A 8336, C.A 8436, PEL 102, PEL 103 and PEL 105

	MODEL	MEASUREMENT RANGE	CLAMPING \varnothing / LENGTH	IEC 61010	REFERENCE
CURRENT SENSORS	 MN93	500 mA to 200 A _{AC}	\varnothing 20 mm	600 V CAT III / 300 V CAT IV	P01120425B
	 MN 93A	5 mA to 100 A _{AC}	\varnothing 20 mm	600 V CAT III / 300 V CAT IV	P01120434B
	 MA193-250 MA193-350 MA196-350	100 mA to 10 kA _{AC}	\varnothing 70 mm / 250 mm \varnothing 100 mm / 350 mm \varnothing 100 mm / 350 mm	1000 V CAT III / 600 V CAT IV	P01120580 P01120567 P01120568
	 PAC93	1 A to 1,000 A _{AC} / 1 A to 1,300 A _{DC}	1 x \varnothing 39 mm or 2 x \varnothing 25 mm	600 V CAT III / 300 V CAT IV	P01120079B
	 J93	50 A to 3,500 A _{AC} / 50 A to 5,000 A _{DC}	\varnothing 72 mm	600 V CAT III / 1000 V CAT IV	P01120110
	 A193-450 A196A-610	100 mA to 10 kA _{AC}	\varnothing 140 mm / 450 mm \varnothing 190 mm / 610 mm	1000 V CAT III / 1000 V CAT IV	P01120526B P01120554
	 A193-800	100 mA to 10 kA _{AC}	\varnothing 250 mm / 800 mm	1000 V CAT III / 600 V CAT IV	P01120531B
	 C193	1 A to 1,000 A _{AC}	\varnothing 52 mm	600 V CAT IV	P01120323B
	 E3N	50 mA to 10 A _{AC/DC} 100 mA to 100 A _{AC/DC}	\varnothing 11.8 mm	600 V CAT III / 300 V CAT IV	P01120043A

	DESCRIPTION	REFERENCE
OTHER ACCESSORIES	 Kit of 5 banana leads + 5 crocodile clips + 1 set of coloured rings	P01295483
	 Kit of 4 banana leads + 4 crocodile clips + 1 set of coloured rings	P01295476
	 1 set of coloured inserts and rings	P01102080
	 5 A adapter unit	P01101959
	 Reeling box - MultiFix magnetized casing	P01102149
	 USB-A USB-B lead	P01295293
	 Bag no. 22	P01298056
	 DataView® software	P01102095
	 ESSAILEC casing	P01102131