

LONG LIFE CUTTING HOLES IN BRICK AND PARTICLE BOARD

EXPERT Construction Material PC Plus Material Hole Saw

EXPERT

- ① Exceptional durability is built in with Bosch Carbide Technology
- ② Ground and sharpened fine carbide teeth for strength, durability and precision
- ③ Efficient chip extraction through large slots



* vs. Bosch 2609256D05



Video



BOSCH

EXPERT CONSTRUCTION MATERIAL PC PLUS HOLE SAW



- ▶ Ideal for cutting neat holes up to 60 mm in depth, for example for tubing for electricians' wires and plumbers' fresh & waste water pipes; holes for sockets, light switches, junction boxes; holes for recessed lighting, fire alarms, presence detectors; or for ducting for cool-air or drying air
- ▶ Best for electricians and plumbers: long lasting and highly versatile
- ▶ Lasts up to 50x longer than Bosch 2609256D05 Hole Saw in tough materials
- ▶ For use with the Bosch Power Change Plus keyless arbor: offering accuracy and robustness



PRODUCT PROPERTIES			ORDERING INFORMATION				
Diameter mm	Working length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
19	60	PC1b	1	1	535 975	2 608 900 451	
20	60	PC1b	1	1	535 982	2 608 900 452	
22	60	PC1b	1	1	535 999	2 608 900 453	
25	60	PC1b	1	1	536 002	2 608 900 454	
30	60	PC1b	1	1	536 019	2 608 900 455	
32	60	PC1b	1	1	536 026	2 608 900 456	
35	60	PC1b	1	1	536 033	2 608 900 457	
38	60	PC1b	1	1	536 040	2 608 900 458	
40	60	PC1b	1	1	536 057	2 608 900 459	
41	60	PC1b	1	1	536 064	2 608 900 460	
44	60	PC1b	1	1	536 071	2 608 900 461	
48	60	PC1b	1	1	536 088	2 608 900 462	
51	60	PC1b	1	1	536 095	2 608 900 463	
54	60	PC1b	1	1	536 101	2 608 900 464	
57	60	PC1b	1	1	536 118	2 608 900 465	
60	60	PC1b	1	1	536 125	2 608 900 466	
64	60	PC1b	1	1	536 132	2 608 900 467	
65	60	PC1b	1	1	536 149	2 608 900 468	
67	60	PC1b	1	1	536 156	2 608 900 469	
68	60	PC1b	1	1	536 163	2 608 900 470	
70	60	PC1b	1	1	536 170	2 608 900 471	
73	60	PC1b	1	1	536 187	2 608 900 472	
76	60	PC1b	1	1	536 194	2 608 900 473	
79	60	PC1b	1	1	536 200	2 608 900 474	
80	60	PC1b	1	1	536 217	2 608 900 475	
83	60	PC1b	1	1	536 224	2 608 900 476	
86	60	PC1b	1	1	536 231	2 608 900 477	
92	60	PC1b	1	1	536 248	2 608 900 478	
98	60	PC1b	1	1	536 255	2 608 900 479	
102	60	PC1b	1	1	536 262	2 608 900 480	
105	60	PC1b	1	1	536 279	2 608 900 481	
111	60	PC1b	1	1	536 286	2 608 900 482	
114	60	PC1b	1	1	536 293	2 608 900 483	
121	60	PC1b	1	1	536 309	2 608 900 484	
127	60	PC1b	1	1	536 316	2 608 900 485	
140	60	C1a	1	1	536 323	2 608 900 486	



BOSCH

EXPERT CONSTRUCTION MATERIAL PC PLUS HOLE SAW

PRODUCT PROPERTIES		ORDERING INFORMATION				
Diameter mm	Working length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
152	60	C1a	1	1	536 330	2 608 900 487
159	60	C1a	1	1	536 347	2 608 900 488



BOSCH