

General Information

Extended Product Type:	332MHS6W
Product ID:	2CMA167856R1000
EAN:	7392696678568
Catalog Description:	Switched interlocked socket-outlet, 6h, 32A, IP67, 3P+E
Long Description:	Switched Interlocked Socket Outlet, horisontal, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Horisontal

Ordering

EAN:	7392696678568
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	168 mm
Product Net Height:	129 mm
Product Net Length:	136 mm
Product Net Depth:	129 mm
Product Net Weight:	0.63 kg

Container Information

Package Level 1 Width:	144 mm
Package Level 1 Length:	202 mm
Package Level 1 Height:	140 mm
Package Level 1 Gross Weight:	0.73 kg
Package Level 1 EAN:	7392696678568
Package Level 1 Units:	1 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, knock-outs Ø25mm/M25
Cable Cross-Section:	2.5 ... 10 mm ²
Cable Entry Position:	Top and bottom
Cable Outlets Per Side:	1xØ25
Color:	Red
Degree of Protection:	acc. to IEC 60529 IP67
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
Function:	Switched interlocked socket outlet, horisontal
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#332MHS6W
Mounting Type:	Horisontal
Number of Poles:	4
Object Classification Code:	2CMT005069
Product Main Type:	MHS
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Watertight
Rated Current (I _n):	32 A
Rated Voltage (U _r):	380 ... 415 V

RoHS Date:	L23
Standards:	IEC 60 309-1, -2, -4
Suitable For:	Switched Interlocked Socket Outlets, Horizontal
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer:	2416948
UNSPSC:	39120000

