

# Extension adapter - ENLAR-M-KV-M25/M32



1647679

<https://www.phoenixcontact.com/gb/products/1647679>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

---

Step-up adapter, M25 to M32, including O-ring



# Extension adapter - ENLAR-M-KV-M25/M32



1647679

<https://www.phoenixcontact.com/gb/products/1647679>

## Commercial Data

Item number	1647679
Packing unit	10 pc
Minimum order quantity	10 pc
Sales Key	BF7DZX
Product Key	BF7DZX
Catalog Page	Page 701 (C-2-2019)
GTIN	4017918947088
Weight per Piece (including packing)	28.52 g
Weight per Piece (excluding packing)	28.52 g
Customs tariff number	74198090
Country of origin	DE

# Extension adapter - ENLAR-M-KV-M25/M32

1647679


<https://www.phoenixcontact.com/gb/products/1647679>

## Technical Data

### Product properties

Product type	Extension adapter
--------------	-------------------

### Dimensions

Dimensional drawing	
Length	21 mm
Length of the connecting thread	6.5 mm
Length without connecting thread	14.5 mm
Connecting thread diameter	25 mm
Hexagon angular dimension	34 mm
Thread type connection side	M25 x 1.5
Thread pitch	1.5 mm
Thread type on seal side	M32

### Material specifications

Color	silver
Material	Brass, nickel-plated
O-ring material	NBR

### Connector

Material	Brass, nickel-plated
Material	Brass, nickel-plated

### Cable / line

#### Cable structure

External cable diameter	20 mm
-------------------------	-------

#### Ambient conditions

Halogen-free	no
--------------	----

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

### Mounting

Assembly instructions	With corresponding screw connection: IP68
-----------------------	---

# Extension adapter - ENLAR-M-KV-M25/M32


1647679

<https://www.phoenixcontact.com/gb/products/1647679>



## Drawings

Dimensional drawing



# Extension adapter - ENLAR-M-KV-M25/M32



1647679

<https://www.phoenixcontact.com/gb/products/1647679>

## Classifications

### ECLASS

ECLASS-9.0	27430314
ECLASS-10.0.1	27430314
ECLASS-11.0	27430314

### ETIM

ETIM 8.0	EC000938
----------	----------

### UNSPSC

UNSPSC 21.0	31163000
-------------	----------

# Extension adapter - ENLAR-M-KV-M25/M32



1647679

<https://www.phoenixcontact.com/gb/products/1647679>

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)