



## COMPACT PNEUMATIC RATCHET WRENCH 3/8"

**RC584**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:01





## DESCRIPTION

### COMPACT PNEUMATIC RATCHET WRENCH 3/8"

A little watchmaking masterpiece, the spindle is guided by two needle bearings with an epicyclic gear train speed reducer. Its variable speed drive adjustable with two fingers is truly a must.

**COMFORTABLE** The handle is designed to hold well in the palm of the hand. This profile provides an area for the thumb and a stop for the thumb providing an excellent grip in two-finger operation. **RELIABLE** The 'O' setup makes it possible to position all the parts and above all the two needle bearings in the same axis which ensures great ratchet reliability. The frame/ratchet housing benefits from a special treatment in order to make it more dust- and particle-resistant. This ratchet is designed for all your maintenance operations in confined spaces, it is also intended for automotive, HGV and bodywork maintenance. Compact ratchet with ergonomic sheathing. Rear exhaust on silencer. Swivel supply coupling (360°). Equipped with variable torque/speed control. Recognised for its perfect ergonomics.

## STANDARDS / DIRECTIVES

2006/42/CE, ISO 15744

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:01



SPECIFIC DATA

Designation	COMPOSITE RATCHET WRENCH 3/8"
Sales reference	RC584
L (mm)	196
Weight (g)	770
l (mm)	50
H (mm)	40
drive square	3/8"
Rotation speed (rpm)	200
Vibration (m/s <sup>2</sup> )	1,8
Noise level (dBa)	79
C mm	6,3
C min mm	1/4"
C mm	41
Maximum input torque Nm	
Guarantee	M2   SAM Equipment and Machine Guarantee

**Guarantee applied**

**M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

