

FEATURES

- Available with 2, 3, 4 & 5 treads
- All supplied with retractable sprung castors within a steel hoof/cover for mobility
- Manufactured from steel offering excellent durability
- Double handrails
- 50 mm swivel castors under a steel hoof
- Supplied with ribbed rubber anti-slip treads and platform
- Powder coated blue

RS PRO 4 Tread Steel Steps 1.03m Platform Height, Blue

RS Stock No.: 669-3734



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing safety wheel along steps from RS PRO, a range of high quality and mobile safety steps ideal for use in a wide range of environments for working at height and accessing higher environments. The robust design is manufactured from steel, offering excellent durability with ribbed rubber treads and platform for enhanced grip. The steps benefit from sprung fitted retractable castor wheels enclosed in a steel cover, allowing the steps to be manoeuvred with ease whilst maintaining stability when weight is applied whilst in use. The steps also feature a safety hand rail, adding an additional level of safety when in use. The steps are available with a range of treads (steps) including 2, 3, 4 and 5.

What sizes are available?

- 2 Tread: 9097066
- 3 Tread: 6693730
- 4 Tread: 6693734
- 5 Tread: 9097075

General Specifications

| | |
|------------------------|---|
| Number of Steps | 4 |
| Material | Rubber, Steel |
| Colour | Blue |
| Applications | Retail, Warehouse, Distribution, Home, Office |
| | |

Mechanical Specifications

| | |
|---------------------------|-------------------------|
| Overall Dimensions | 1745mm x 610mm x 1010mm |
| Overall Height | 1745mm |
| Overall Width | 610mm |
| Overall Depth | 1010mm |
| Weight | 27kg |

| Platform Dimensions | |
|---------------------|--------|
| Height | 1045mm |
| Top Tread Width | 380mm |
| Top Tread Depth | 280mm |



| No. Of Treads | Overall H x W x D (mm) | Tread W x D (mm) | Top Tread W x D (mm) | Platform Height (mm) | Average Working Height (mm) | RS Stock No |
|---------------|------------------------|------------------|----------------------|----------------------|-----------------------------|-------------|
| 2 | 1185 x 580 x 615 | 380 x 180 | 380 x 280 | 508 | 2000 | 9097066 |
| 3 | 1440 x 635 x 805 | 380 x 180 | 380 x 280 | 795 | 2320 | 6693730 |
| 4 | 1745 x 610 x 1010 | 380 x 180 | 380 x 280 | 1045 | 2570 | 6693734 |
| 5 | 1940 x 580 x 1120 | 380 x 180 | 380 x 280 | 1270 | 2770 | 9097075 |