



MASTER Value Glass LED bulbs

MASTERVLELED Bulb DT5.9-60W E27 927A60CL G UK

Featuring a classic heritage design, these filament LED bulbs combine the familiar shapes of incandescent bulbs with the benefits of long-lasting LED technology. These MASTER Value Glass LED bulbs offer more energy savings than normal glass LED bulbs. At the same time, they also provide customers with good light experience, enhanced by excellent dimming performance (dimmable glass LED bulbs). MASTER Value Glass LED Bulbs deliver significant energy savings, using 30% less energy compared to normal LED bulbs and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmable LED bulbs also reduce maintenance costs.


Product data

General information		Colour consistency	
Cap base	E27 [E27]	Colour rendering index (nom.)	90
EU RoHS compliant	Yes	LLMF at end of nominal lifetime (nom.)	70 %
Nominal lifetime (nom.)	15000 h	Operating and electrical	
Switching cycle	20000		
Tier	MASTER Value	Input frequency	50 to 60 Hz
Light technical		Power (Rated) (Nom)	5.9 W
Colour Code	922-927 [CCT of 2,200 K-2,700 K]	Lamp current (nom.)	40 mA
Luminous flux (nom.)	806 lm	Wattage equivalent	60 W
Colour designation	Warm Glow (WG)	Starting time (nom.)	0.5 s
Correlated Colour Temperature (Nom)	2200 2700 K	Warm-up time to 60% light (nom.)	0.5 s
Luminous efficacy (rated) (nom.)	136 lm/W	Power factor (nom.)	0.6

MASTER Value Glass LED bulbs


Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	70 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Lamp Finish	Clear
Bulb shape	A60 [A 60mm]
Approval and application	
Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	6 kWh

Dimensional drawing



MASTERVLEEDBulbDT5.9-60W E27 927A60CL G UK


Photometric data



Spectral Power Distribution Colour

	1109131
Product data	
Full product code	871951432473201
Order product name	MASTERVLEEDBulbDT5.9-60W E27 927A60CL G UK
EAN/UPC – product	8719514324732
Order code	32473201
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929003010398
Net Weight (Piece)	0.030 kg


Product	D	C
MASTERVLEEDBulbDT5.9-60W E27 927A60CL G UK	60 mm	104 mm



Light Distribution Diagram

MASTER Value Glass LED bulbs


Photometric data




Colada-Rubio et al. 4.5 Polys Lighting B.V. Page 1/1

General uniform lighting

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram

