




---

 PRODUCT-DETAILS

## 2621 WDI

Switch Push button, Single push button 1P  
1NO blue - Busch-Duro 2000 WDI




---

### General Information

|                       |  |
|-----------------------|--|
| Extended Product Type | 2621 WDI   |
| Product ID            | 2CKA001483A0171  |
| EAN                   | 4011395056004  |
| Catalog Description   | Switch Push button, Single push button 1P 1NO blue - Busch-Duro 2000 WDI                   |
| Long Description      | IP 66 only in connection with respective symbols. Delivery without symbol With N terminal. |

---

### Installation

|                             |                     |
|-----------------------------|---------------------|
| Instructions and Manuals    | No document needed  |
| Wiring Diagram              | 2CKA000097E0046     |
| Mounting Type               | Surface Mounted     |
| Type of Fastening           | Mounting with Screw |
| Modular Components Included | Complete Device     |

## Environmental

|                      |      |
|----------------------|------|
| Degree of Protection | IP66 |
|----------------------|------|

## Technical

|                                   |                    |
|-----------------------------------|--------------------|
| Data Sheet, Technical Information | No document needed |
| Contacts Configuration            | 1 NO, 0 NC         |
| Number of Poles                   | 1P                 |
| Number of Rocker Switches         | 1                  |
| Actuator Type                     | Push button        |

## Electrical

|                         |       |
|-------------------------|-------|
| Rated Voltage ( $U_r$ ) | 250 V |
| Rated Current ( $I_n$ ) | 10 A  |
| Number of Contacts NO   | 1     |

## Design

|                      |                     |
|----------------------|---------------------|
| Design Range         | Busch-Duro 2000 WDI |
| Surface Finishing    | Untreated<br>Matt   |
| Material             | Thermoplastic       |
| Label Space Provided | Without Label Space |
| RAL Number           | Similar to RAL 5010 |
| Color                | blue                |

## Dimensions

|                            |                 |
|----------------------------|-----------------|
| Product Net Width          | 74 mm           |
| Product Net Height         | 93 mm           |
| Product Net Depth / Length | 54 mm           |
| Product Net Weight         | 160 g           |
| Dimension Diagram          | 2CKA000097E0614 |

## Material Compliance

|   |  |
|---|--|
| RoHS Declaration                            | 2CKA200000E0446  |
| RoHS Information                            | Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019 |
| REACH Declaration                           | 2CKA309999E9999  |
| REACH Information                           | True - contains substances > 0.1 mass percentage                       |
| REACH Date                                  | 20250901   |
| Conflict Minerals Reporting Template (CMRT) | 9AKK108468A3363  |
| SCIP  | f49e6368-1464-40c6-ac41-c99dfcc79bdb Germany                           |
| Simplified SCIP                             | f49e6368-1464-40c6-ac41-c99dfcc79bdb Germany                           |
| WEEE Category                               | 5. Small Equipment (No External Dimension More Than 50 cm)             |
| WEEE B2C / B2B                              | Business To Consumer   |

## Certificates and Declarations

|  |                 |
|--|-----------------|
| Declaration of Conformity - CE           | 2CKA100000E0334 |
| EU Data Act Applicability and Compliance | Not Applicable  |

## External Classifications and Standards

|         |                        |
|---------|------------------------|
| ETIM 9  | EC000029 - Push button |
| ETIM 10 | EC000029 - Push button |
| eClass  | V11.0 : 27144044       |

## Accessories

| Identifier      | Description  | Type    | Quantity | Unit Of Measure |
|-----------------|--|---------|----------|-----------------|
| 2CKA001716A0042 | Mounting Plate 1-gang brass  | 2609 WS | 1        | piece           |
| 2CKA001714A0229 | Symbol for rocker with Symbol "bell" transparent                                   | 2145 KI | 1        | piece           |
| 2CKA001714A0211 | Symbol for rocker with Symbol "light" transparent                                  | 2145 LI | 1        | piece           |
| 2CKA001714A0203 | Symbol for rocker with Neutral symbol transparent                                  | 2145 N  | 1        | piece           |
| 2CKA001714A0237 | Symbol for rocker with Symbol "key" transparent                                    | 2145 TR | 1        | piece           |
| 2CKA001714A0245 | Symbol for rocker with Neutral symbol red transparent                              | 2145-12 | 1        | piece           |
| 2CKA001784A0016 | Illumination set for Switch/push button Orange Neon lamp, 0.6 mA, 230 V            | 8332-1  | 1        | piece           |
| 2CKA001784A0024 | Illumination set for Switch/push button White Incandescent lamp, 40 mA, 3 ... 8 V  | 8333-1  | 1        | piece           |
| 2CKA001784A0529 | Illumination set for Switch/push button White Incandescent lamp, 40 mA, 12 V       | 8335-1  | 1        | piece           |
| 2CKA001784A0040 | Illumination set for Switch/push button Orange Neon lamp, 0.6 mA, 230 V            | 8339-1  | 2        | piece           |
| 2CKA001784A0321 | Illumination set for Switch/push button Orange Neon lamp, 1 mA, 230 V              | 8346-1  | 1        | piece           |
| 2CKA001784A0719 | Illumination set for Switch/push button White Incandescent lamp, 40 mA, 24 V AC/DC | 8358    | 1        | piece           |
| 2CKA001761A0808 | Cable Entry blue   | 2081    | 1        | piece           |
| 2CKA001761A0782 | Cable Entry blue   | 2079    | 1        | piece           |
| 2CKA001761A1368 | Cable Entry grey   | 2070    | 1        | piece           |
| 2CKA001761A1376 | Cable Entry grey   | 2071    | 1        | piece           |

## Categories

Low Voltage Products and Systems → Wiring Accessories - Light Switch Ranges → Surface Mounted Range → Mechanical Controls

