



**NF E 74.303**


| art.      | Ø mm      | Ø mm  | L mm | Ø1 mm | A mm | A1 mm | L1 mm | g    |
|-----------|-----------|-------|------|-------|------|-------|-------|------|
| 009330006 | 933 6X6   | 6x6   | 11,5 | 110   | 5,0  | 8,0   | 15,0  | 55   |
| 009330007 | 933 7X7   | 7x7   | 12,5 | 116   | 6,0  | 9,0   | 18,0  | 60   |
| 009330008 | 933 8X8   | 8x8   | 13,0 | 120   | 6,0  | 11,0  | 20,0  | 65   |
| 009330009 | 933 9X9   | 9x9   | 14,0 | 125   | 7,0  | 11,0  | 20,0  | 75   |
| 009330010 | 933 10X10 | 10x10 | 16,5 | 133   | 8,0  | 13,0  | 22,0  | 105  |
| 009330011 | 933 11X11 | 11x11 | 17,5 | 143   | 8,5  | 14,0  | 23,0  | 125  |
| 009330012 | 933 12X12 | 12x12 | 19,0 | 148   | 8,5  | 14,0  | 25,0  | 165  |
| 009330013 | 933 13X13 | 13x13 | 19,5 | 154   | 9,5  | 16,0  | 28,0  | 175  |
| 009330014 | 933 14X14 | 14x14 | 21,5 | 167   | 10,0 | 17,0  | 28,0  | 220  |
| 009330015 | 933 15X15 | 15x15 | 22,5 | 182   | 10,0 | 17,0  | 29,0  | 235  |
| 009330016 | 933 16X16 | 16x16 | 24,5 | 193   | 11,0 | 20,0  | 33,0  | 335  |
| 009330017 | 933 17X17 | 17x17 | 26,0 | 198   | 12,0 | 20,0  | 34,0  | 340  |
| 009330018 | 933 18X18 | 18x18 | 26,5 | 215   | 13,0 | 20,0  | 34,0  | 370  |
| 009330019 | 933 19X19 | 19x19 | 29,0 | 220   | 14,0 | 22,0  | 35,0  | 435  |
| 009330020 | 933 20X20 | 20x20 | 30,5 | 222   | 14,0 | 22,0  | 37,0  | 485  |
| 009330021 | 933 21X21 | 21x21 | 30,5 | 236   | 16,0 | 25,0  | 39,0  | 575  |
| 009330022 | 933 22X22 | 22x22 | 32,5 | 250   | 16,0 | 25,0  | 41,0  | 610  |
| 009330023 | 933 23X23 | 23x23 | 33,5 | 256   | 17,0 | 26,0  | 44,0  | 705  |
| 009330024 | 933 24X24 | 24x24 | 35,0 | 272   | 19,0 | 27,0  | 46,0  | 805  |
| 009330025 | 933 25X25 | 25x25 | 36,5 | 282   | 19,0 | 27,0  | 47,0  | 895  |
| 009330026 | 933 26X26 | 26x26 | 37,5 | 296   | 20,0 | 28,0  | 47,0  | 950  |
| 009330027 | 933 27X27 | 27x27 | 39,0 | 296   | 21,0 | 28,0  | 50,0  | 1220 |
| 009330028 | 933 28X28 | 28x28 | 39,0 | 314   | 22,0 | 28,0  | 51,0  | 1235 |
| 009330030 | 933 30X30 | 30x30 | 42,5 | 348   | 23,0 | 31,0  | 51,0  | 1520 |
| 009330032 | 933 32X32 | 32x32 | 45,5 | 364   | 24,0 | 32,0  | 51,0  | 1800 |