



Measurement has never been so easy as it is with the DLE 150.

The days of complicated and tedious measurement are over once and for all: the DLE 150 has arrived. It allows you to achieve more exact measurement results than ever before at the press of a button using a laser beam. Up to a distance of 150 metres and precise to within a few millimetres thanks to an abundance of useful functions that are operated with easy-to-understand symbols and can be read on the clear display. The professional tool for a professional job.

Die Zeiten umständlicher und langwieriger Messungen sind endgültig vorbei: Der DLE 150 ist da. Per Laserstrahl erzielen Sie damit auf Knopfdruck so exakte Messergebnisse wie noch nie. Bis zu einer Entfernung von 150 Metern und bis auf wenige Millimeter genau. Dank einer Vielzahl sinnvoller Funktionen, die Sie mit einfach verständlichen Tasten bedienen und auf dem übersichtlichen Display ablesen können, macht das Arbeiten mit dem DLE 150 richtig Spaß. Auch wenn Sie das bei dieser Arbeit gar nicht erwartet hätten.

BOSCH

Performance range

A wide range of benefits that are easy to see

Specifications:


- Easy and precise measurement of lengths, areas and volumes using a laser beam
- Up to a distance of 150 metres and precise to within a few millimetres
- An abundance of practical functions
- Easy to operate with a clear display
- Small and handy

The professional tool for a professional job:

- Continuous measurement: transfers specified dimensions
- Minimum measurement: determines the shortest distance, e.g. horizontal from wall to wall
- Maximum measurement: determines the largest distance, e.g. diagonal of a room
- Indirect length measurement, e.g. determining the height of a house. Quick and easy by pressing a button twice.
- Vial for easy horizontal alignment.
- Universal end piece for measurements from corners, surfaces and edges - convenient and precise.
- Easy, self-explanatory operation
- Easy-to-use key assignment
- Clear and easy-to-read display
- Illuminating display for easy reading.

The DLE 150 is an essential measuring tool for:

- All professionals who measure dimensions and distances
- Building contractors, structural engineers, civil engineers, ...
- Architects, surveyors, estate agents, stress analysts...



Small, light, handy



Universal end piece for measurements from corners, surfaces and edges - convenient and precise.

BOSCH

Details

Specifications, Comes complete with, Accessories

Specifications:

Order Number	EU-Version: 0 601 098 303 UK-Version: 0 601 098 342
Measuring range	from 0,3 m to 150 m
Accuracy, typical	+/-2 mm (0,3....30 m); max. +/-3 mm
Measuring time, typical	<0,5 s; max. 4 s
Laser type	635 nm, <1 mW
Laser class	2
Batteries	4 x 1.5V LR6 (AA) or rechargeable 4 x 1.2V KR6 (AA). Approx. 30,000 individual measurements can be made with one battery life.
Protection class	IP54 (dust and splash-proof)
Tripod thread	1/4 "



Comes complete with:

- universal and compact-end piece
- Vial
- Protective case
- 4 batteries Typ LR 6 (AA) Varta Made in Germany

Special Accessories:

- High-quality laser-goggles part number: 2 607 990 031
- Target plate for large distances part number: 2 607 001 391