


## 846 3-flute Countersink Bit, 12.40 x 35 mm

Bit Sets for Special Applications



<b>EAN:</b>	4013288101471	<b>Size:</b>	143x55x24 mm
<b>Part number:</b>	05104633001	<b>Weight:</b>	21 g
<b>Article number:</b>	846 HSS	<b>Country of origin:</b>	CN
		<b>Customs tariff number:</b>	82075060

- Hex shaft for very good power transfer
- Finely-tuned material elasticity for great durability
- Very good centring properties
- Perfect chip removal
- Precise return movement

High quality 3-flute countersink bit for deburring, chamfering and countersinking. A finely-tuned material elasticity provides for great durability. Perfect chip removal and a low tilt risk ensure pleasant working. Cutting section as per DIN 335-C, 90° with 3 cutters. ¼" hexagon, suitable for holders with take-up as per DIN ISO 1173-D 6.3.


### Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_and\\_sets\\_bit\\_sets\\_bit\\_sets\\_for\\_special\\_applications\\_846\\_hss.html](https://products.wera.de/en/bits_holders_adaptors_and_sets_bit_sets_bit_sets_for_special_applications_846_hss.html)

Wera - 846 HSS  
05104633001 - 4013288101471





Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

3-flute countersink bits



3-flute countersink bits, 90° • Application: Deburring, chamfering and countersinking • ¼" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173) • Hexagon shaft for very high torque transfer • HSS = high speed steel • Finely adjusted material elasticity for long service life • 3 tips • Excellent centring properties • Straightforward cutting • Perfect chip removal • Low jamming risk • Precise return control • High corrosion protection

Further versions in this product family:

	 mm	 mm	 mm	
05104630001	6.30	20.00	31.0	M 3
05104631001	8.30	20.00	31.0	M 4
05104632001	10.40	20.00	34.0	M 5
<b>05104633001</b>	<b>12.40</b>	<b>20.00</b>	<b>35.0</b>	<b>M 6</b>
05104634001	16.50	20.00	40.0	M 8
05104635001	20.50	20.00	41.0	M 10

Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_and\\_sets\\_bit\\_sets\\_bit\\_sets\\_for\\_special\\_applications\\_846\\_hss.html](https://products.wera.de/en/bits_holders_adaptors_and_sets_bit_sets_bit_sets_for_special_applications_846_hss.html)

Wera - 846 HSS  
05104633001 - 4013288101471

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de