

Product datasheet

Specifications



Kaedra XT - versatile enclosure with blank part - 1 x 16 modules

KDR35165

 **Discontinued on:** 15 Aug 2024

EAN Code: 3606480697777

 **Discontinued**

Main

| | |
|---------------------------|------------------------|
| Range | Kaedra |
| product name | Kaedra XT |
| Product or component type | Weatherproof enclosure |
| Enclosure type | Versatile enclosure |

Complementary

| | |
|---------------------------------|-------------------------------------|
| Enclosure mounting | Surface |
| 9 mm pitches | 32 |
| Number of 18 mm modules per row | 16 |
| Total number of 18 mm modules | 16 |
| Number of horizontal rows | 1 |
| Electrical insulation class | Class II Double insulation |
| Type of front cover | Smoked |
| [In] rated current | 90 A |
| Type of rail | DIN |
| Cable entry | : knock-out |
| Locking options description | With key |
| Enclosure material | Housing: self-extinguishing polymer |
| Width | 320 mm |
| Height | 400 mm |
| Depth | 125 mm |
| Colour | Light grey (RAL 7035) |

Environment

| | |
|-------------------------|------------------------------------|
| Standards | EN 62262 |
| Fire resistance | 850 °C conforming to IEC 60695-2-1 |
| IP degree of protection | IP65 conforming to IEC 60529 |
| IK degree of protection | IK09 conforming to EN 50102 |
| Mechanical robustness | Shocks conforming to ISO 179-1 A1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|---|
| Environmental characteristics (UV) | Ultraviolet degradation test conforming to ISO 4892-2:2013 UV resistant: class 5 conforming to ISO 4582:2010 |
| Ambient air temperature for operation | -25...60 °C |

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 15.000 cm |
| Package 1 Width | 34.000 cm |
| Package 1 Length | 41.000 cm |
| Package 1 Weight | 2.334 kg |
| Unit Type of Package 2 | P12 |
| Number of Units in Package 2 | 42 |
| Package 2 Height | 80.000 cm |
| Package 2 Width | 80.000 cm |
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 110.028 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

| Materials and Substances | |
|--------------------------|--------------------------------------|
| SCIP Number | B7c6f1d6-d622-4f6c-907b-f4c3173076cb |