





KLINGERstatite is an impregnated paper gasket providing reliable sealing at low cost for applications where the additional strength offered by fibre reinforcements such as aramid, glass or carbon is not a requirement. Paper-based materials are often used in low-temperature and low-pressure applications.

The Klinger group has been recognised as the market leader in gaskets and sealing for over a century. Our research and development laboratories have investigated over 250 different fibre forms in the search for asbestos free alternatives. The search has resulted in a range of high quality and high performance asbestos free materials that have been proven in service

KLINGERstatite is based on cellulose fibre and can be supplied in sheet, roll or gasket form. It is extensively used in the automotive industry where its excellent oil and fuel resistance provides long lasting and reliable sealing at low cost.

GENERAL PROPERTIES

- » Available in roll form
- » Excellent chemical resistance
- » High compressibility

AVAILABILITY

» Thickness (mm): 0.15, 0.2, 0.25, 0.4, 0.5, 0.8, 1.0,

1.6, 3.2

» Sheeting (m): 1.0 x 1.0

Also available in rolls:

THICKNESS (MM)	0.15	0.2	0.25	0.4	0.5	0.8	1.0	1.6	3.2
ROLL LENGTH (M)	100	100	100	100	100	100	50	50	25



TYPICAL SPECIFICATION

(Based on 0.8mm thick sample)

PROPERTIES	VALUES		
Min. Tensile Strength (ASTM F152)	>13N/mm ²		
Compressibility (ASTM F 36 G)	25-40%		
Recovery (ASTM F 36 G)	0.4 %		
Max. continuous service temp.	120°C		
Max. Pressure	8 Bar		
Weight increase after fluid:			
Oil IRM 903, 5h/150°C	<15%		
Fuel B, 5h/23°C	<15%		
Water, 5h/23°C	<90%		
Thickness increase after fluid:			
Oil IRM 903, 5h/150°C	<5%		
Fuel B, 5h/23°C	<5%		
Water, 5h/23°C	<30%		
Density	0.7g/cm ³		

HEAD OFFICE KLINGER Ltd Wharfedale Road

Euroway Trading Estate Bradford BD4 6SG

AS/EN 9100 Series Aviation, Space and Defense

ISO 9001 Quality Manage OHSAS 18001 Occupational Health & Safety Management

Tel: 01274 688 222

Fax: 01274 688 549

enquiries@klingeruk.co.uk

www.klinger.co.uk

ISO 14001

EMS 570165

FM 602916 FM 10571 OHS 570166 KLINGER RUNCORN

Tel: 01928 577 030 Fax: 01928 575 233

KLINGER SOUTHAMPTON

Tel: 02380 611 855 Fax: 02380 610 360 KLINGER ABERDEEN

Tel: 01224 772 962 Fax: 01224 772 953 KLINGER IMMINGHAM

Tel: 01469 575 289 Fax: 08449 676 779

KLINGER MIDDLESBROUGH

Tel: 01642 220 289 Fax: 01642 220 290

KLINGER GRANGEMOUTH

Tel: 01324 472 231 Fax: 01324 482 111