

---

TVIP11552

## IR HD 720p WLAN Network Compact Camera

All product information will be available soon.



---

### Product highlights:

- 1/4" progressive scan CMOS sensor
  - Max. resolution 1280 x 720 pixels, 720p
  - 6 integrated IR LEDs for day/night function
  - Simultaneous transmission of MPEG-4, MJPEG, H.264, and 3GP video data (quad stream)
  - MicroSD card slot
  - Built-in sensors for motion and sound
  - Storage of the video data on NAS/network drives
  - Installed microphone
  - WLAN interface IEEE 802.11b/g/n
- 

**Your Partner:**  
**ABUS-TEST**  
Linker Kreuthweg 5  
86444 Affing  
+49 (8207) 959900

TVIP11552

# IR HD 720p WLAN Network Compact Camera

Technical Data			
Sensor	1/4" Progressive Scan CMOS Sensor	Power consumption	440mA
Camera type	day / night	Protection	IP34
Resolution	1280 x 720, 640 x 480, 320 x 280, 160 x 160	Dimensions (WxHxD)	67 x 111 x 45
Image elements	1280(H) x 720(V)		
Lens	F1.5, 4.0		
Horizontal angle of view	53°		
Digital zoom	10		
Day/night switch	IR cut can be swivelled electromagnetically		
Minimum illumination (color)	0,5 lux		
Minimum illumination (IR)	0		
Images per frame	MJPEG: 25 pictures/s @ 1280 x 720, MJPEG: 25 pictures/s @ 640 x 480, MPEG-4: 15 pictures/s @ 1280 x 720, MPEG-4: 25 pictures/s @ 640 x 480, H.264: 25 pictures/s @ 1280 x 720, H.264: 25 pictures/s @ 640 x 480		
Number of parallel streams	4 (MJPEG, MPEG-4, H.264, 3GPP)		
Electronic-Shutter	1~1/7780 seconds		
White balance	yes		
Amplifier control	0-9		
Backlight compensation	BLC, WDR		
Motion detection	3 zones		
Pre-/post-alarm storage	3 pre-alarm, 1 event, 3 post-alarm picture		
Alarm input	2		
Microphone	yes		
Alarm	E-Mail / FTP / HTTP info / network drive		
Supported software	ABUS VMS, Internet Explorer 6 or higher, Safari, Mozilla Firefox		
IR LEDs	6		
IR range	5m		
Network connection	RJ45 LAN, 802.11 b/g/n WLAN		
Network protocol	Bonjour, TCP/IP, DHCP, PPPoE, ARP, ICMP, FTP, SMTP, DNS, NTP, UPnP, RTSP, RTP, HTTP, TCP, UDP, 3GPP/ISMA RTSP		
Encryption	HTTPS SSLv3, WEP 64/128bit, WPA/WPA2-PSK		
Power supply	5V DC		

**Your Partner:**  
**ABUS-TEST**  
 Linker Kreuthweg 5  
 86444 Affing  
 +49 (8207) 959900