



150 TOOLS IN FOAM MODULE

CP-150-ET

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:15





DESCRIPTION

150 TOOLS IN FOAM MODULE

This workbench foam module composition includes a comprehensive set of 150 mechanical tools, carefully organized to meet the demands of professional workshops. Designed to deliver versatility, efficiency, and working comfort, it covers all common maintenance, assembly, and repair operations.

The modules include a wide selection of metric combination wrenches, 1/4" and 1/2" sockets, along with associated accessories such as ratchets, extensions, universal joints, sliding T-handles, reducers, and adapters, ensuring maximum flexibility during use. Fastening requirements are covered by a complete range of bit sockets, driver bits, standard and Torx® screwdrivers, as well as Resistorx® hex and Torx® keys.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:15



The set is further completed with striking and cutting tools (engineer's hammer, soft-face hammer with interchangeable inserts, cold chisel, hand shears, pliers), measuring and inspection tools (steel rule, feeler gauges), and practical daily-use accessories such as a pen light, safety retractable knife, and a crimping tool.

The foam modules provide clear visual organization, optimal tool protection, and immediate time savings, while also making it easy to identify missing tools. An ideal solution for a structured, durable, and high-performance workstation.

SPECIFIC DATA

Designation	SET OF 150 TOOLS IN FOAM MODULE FOR ETAB-120
Sales reference	CP-150-ET
Weight (kg)	11.5
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset

	x 12	Combination wrenches in mm 50A-... Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 19 - 21 mm
	x 18	1/2" short hexagonal sockets in mm SH-... Ref : 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32 mm
	x 1	Straight 1/2" extensions S-2... Ref : S-210

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:15



	x 1	1/2" sliding locking handle S-120
	x 1	1/2" site ratchet with lever reversion S-157B
	x 1	Site 1/4" ratchet R-157B
	x 1	1/4" sliding handle R-120
	x 1	1/4" joint R-240
	x 1	Straight 1/4" extensions R-21... Ref : R-210
	x 1	Fitted 1/4" extension R-225
	x 1	Fitted 1/4" extension R-225C
	x 1	1/4" bit holder socket RD-1
	x 10	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 4 - 5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
	x 6	1/4" single-piece screwdriver sockets for hollow hexagonal screws RS-... Ref : 3 - 4 - 5 - 6 - 7 - 8 mm
	x 5	1/4" sockets for Torx® head RTX-... Ref : 4 - 5 - 6 - 7 - 8 mm
	x 8	One-piece screwdriver socket 1/4" for Torx® mark RT-... Ref : T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 1	1/4" adapter R-232

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:15



	x 1	1/2" adapter S-232
	x 1	1/2" reducer S-230
	x 1	31-piece screwdriver bit set E900-J30B
	x 1	Flexible rules 781-... Ref : 781-2
	x 5	Long drift punches 7-...A Ref : 7-25A - 7-35A - 7-50A - 7-70A - 7-90A
	x 1	Punch 10 mm 8N-...A Ref : 8N-3A
	x 1	Satin-finish adjustable wrenches 54-C... Ref : 54-C10
	x 1	Rack of 9 Resistorx® male keys 59-R9A
	x 9	ResisTorx® elbow hexagonal keys 59-... Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 1	Polished burnished finish stacked-branch multigrip pliers 209-25PA
	x 1	Chrome-plated polished diagonal cutting pliers 232-...G Ref : 232-16G
	x 1	Riveting hammers 310-...N Ref : 310-32N
	x 1	Bodyworker's chisel 1-... Ref : 1-B
	x 1	Self-retracting blade knife 378-40

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:15



	x 1	Pen light 1396-LS
	x 1	Crimping pliers 241-42
	x 1	Thickness gauges 770-... Ref : 770-E
	x 1	Universal hand shears 331-16
	x 1	Mallets with interchangeable tips 320-...D Ref : 320-35D
	x 1	Spare tips for mallets 320-...d and 322 320-C-...N / 322-C-...
	x 6	Torx® screwdriver TA-...X Ref : T10 - T15 - T20 - T25 - T30 - T40
	x 2	Electrician's slotted screwdriver TA-...E Ref : 3x50 - 6.5x150 mm
	x 1	Mechanic's slotted screwdriver TA-...M Ref : 5.5x150 mm
	x 3	Phillips® screwdriver TA-...P Ref : N°0 - N°1 - N°2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:15

