

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - 12JUN2016 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		REVISED PER ECO-19-006961	06MAY2019	AP	AC



2304883-6	2 DETECT PIN	2000±20
2304883-4	NO DETECT PIN	250±10
2304883-3	1 LEFT DETECT PIN	250±10
2304883-2	1 RIGHT DETECT PIN	250±10
2304883-1	2 DETECT PIN	250±10
TE P/N	DESCRIPTION	L

WIRING CHART

FROM	WIRE COLOR	TO
J1-P2	BLACK	J2-P2
J1-P1	RED	J2-P1

AR	AR	AR	AR	AR	MR	WIRE, AWG10, RED	4
AR	AR	AR	AR	AR	MR	WIRE, AWG10, BLACK	3
4	4	4	4	4	PC	ET CONTACT, AWG10	2
-	2	-	-	-	PC	ET HSG, 2 POS, SHORT PULL-TAB, NO DETECT PIN	1
-	-	2	-	-	PC	ET HSG, 2 POS, SHORT PULL-TAB, 1 LEFT DETECT PIN	
-	-	-	2	-	PC	ET HSG, 2 POS, SHORT PULL-TAB, 1 RIGHT DETECT PIN	
2	-	-	-	2	PC	ET HSG, 2 POS, SHORT PULL-TAB, 2 DETECT PIN	
-6	-4	-3	-2	-1	U/M	DESCRIPTION	ITEM

NOTES:
 1. 100% ELECTRICAL TEST FOR CONTINUITY, OPENS AND SHORTS.

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY ENVIRONMENTAL STANDARD TEC-138-702

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ADAM CHEN 12JUN2016	TE TE Connectivity	
DIMENSIONS: mm		CHK - APVD DAVID ZHANG 12JUN2016		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME Cable AssY, ET 2POS, SHORT PULL-TAB	RESTRICTED TO -	
MATERIAL -		FINISH -	SIZE A2	CAGE CODE 00779
		WEIGHT 0	DRAWING NO C=2304883	SCALE N.T.S.
		CUSTOMER DRAWING		SHEET 1 of 1