



Part Number : [2002187000](#)

Product Description : Hand Crimp Tool for SL Crimp Terminals, 30-24 AWG

Series Number : 207129

Status : Active

Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[2002187000-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for SL Crimp Terminals, 30-24 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	SL
Tool Type	Hand Crimp Tool
UPC	195842130685
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Applicable Parts

Description	Part Number
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Reel	<u>16020069</u>
SL Crimp Terminal, Series 70021, Male, with 0.38µm Selective Gold (Au) Plated Contact, 30-24 AWG, Reel	<u>16020077</u>
SL Crimp Terminal, Series 70021, Male, with 0.76µm Selective Gold (Au) Plated Contact, 30-24 AWG, Reel	<u>16020078</u>
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	<u>16020082</u>
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	<u>16020083</u>
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Bag	<u>16020096</u>
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Bag	<u>16020097</u>
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Bag	<u>16020098</u>
SL Crimp Terminal, Series 70021, Male, with Tin (Sn) Plated Contact, 30-24 AWG, Reel	<u>16020105</u>
SL Crimp Terminal, Series 70021, Male, with Tin (Sn) Plated Contact, 30-24 AWG, Bag	<u>16020108</u>
SL Crimp Terminal, Series 70021, Male, with 0.38µm Selective Gold (Au) Plated Contact, 30-24 AWG,	<u>16020109</u>

Bag	
SL Crimp Terminal, Series 70021, Male, with 0.76µm Selective Gold (Au) Plated Contact, 30-24 AWG, Bag	<u>16020110</u>
SL Crimp Terminal, Series 70021, Male, with 0.76µm Selective Gold (Au) Plated Contact, 24-22 AWG, Bag	<u>16020117</u>
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 30-24 AWG, Reel	<u>16020119</u>
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 30-24 AWG, Bag	<u>16021109</u>
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 30-24 AWG, Reel	<u>16021112</u>
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 30-24 AWG, Bag	<u>16021116</u>
SL Crimp Terminal, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	<u>700580082</u>
SL Crimp Terminal, Female, 30-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	<u>700580083</u>
SL Crimp Terminal, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Bag	<u>700580097</u>
SL Crimp Terminal, Female, 30-24 AWG, with 1.27µm Selective Gold (Au) Plated Contact, Reel	<u>700580139</u>
SL Crimp Terminal, Female, 30-24 AWG, with 1.27µm Selective Gold (Au) Plated Contact, Bag	<u>700580140</u>
SL Crimp Terminal, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Reel	<u>700581069</u>

