

Warning label, pre-printed, L=200.00mm, yellow, pack=10pcs.

Art.-No. 597-65200 | WS5-A-150-YE | 



- Permanently marked with the highest quality print
- Self-adhesive vinyl film guarantees a high level of security
- Symbols can have additional text added as required (ATWS)
-
-



More products in this product group:

[Warning signs \(DIN4844 and BGV A8\) >](#)

Application	warning signs that match stringent regulatory requirements for hazardous areas.
Chem. Material Properties	Resistant to oils, water and solvents; flame-retarding
Colour	Yellow (YE)
Colour of Print	Black (BK)
For Size	5
Material	Type 150, Vinyl (150)
PART DESCRIPTION	WS5-A-150-YE
Pack Content	10 pcs.
Package Content packed in	pack
Product Family	HELASIGN, Material 150
Product Group	Warning signs (DIN4844 and BGV A8)
Self adhesive (Yes/No)	Yes
Type	WS5-A

Product Dimensions

Length (L)	200.00 mm
Thickness (T)	80.0 µm
Thickness of Foil	80
Thickness of foil test method	ASTM D3652-83
Width of Liner (WL)	200.00 mm

Adhesive	Acrylic
Curing Temperature	from +10 °C
ELV compliant (Article 4 - 2)	YES
Halogen-free	No
Hazardous Goods	No
Initial tack	110 g/cm ²
Initial tack	ASTM D2979-71
Operating Temperature	-40 °C to +80 °C
Peel strength	550 N/m
Peel strength test method	PSTC 7
Pre-Printed	Yes
ROHS compliant	Yes
Shear strength	120 h
Shear strength test method	FINAT FTM 7
Shelf Life	Minimum 1 year upon receipt / maximal 2 years after production date.
Specifications	



GTIN-13 / EAN	4031026181219
Labels per Sheet	1 pc.
Packaging 1 - Height (m)	0.006 m
Packaging 1 - Length (m)	0.35 m
Packaging 1 - Qty	10
Packaging 1 - Type	bag
Packaging 1 - Volume (m³)	0.000462 m³
Packaging 1 - Weight (kg)	0.020001 kg
Packaging 1 - Width (m)	0.22 m
Packaging 3 - Height (m)	0.24 m
Packaging 3 - Length (m)	0.55 m
Packaging 3 - Qty	500
Packaging 3 - Type	carton
Packaging 3 - Volume (m³)	0.0515 m³
Packaging 3 - Weight (kg)	10.5 kg
Packaging 3 - Width (m)	0.39 m
Sheets per Pack	10 pcs.
Storage Temperature	+21 °C
Storage conditions	50% relative humidity., The storage in the original packaging is recommended., Please avoid warehousing under impacts such as high humidity, heat and coldness.

More Information

