

Product Datasheet uvex 1 8531.7-9 + 0 S1 SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth****Product information**

- Sporty, multifunctional safety shoe
- Especially lightweight and flexible
- The latest generation of 100% metal-free uvex xenova® toe cap, compact design, anatomical shape, good side stability, no thermal conductivity and antimagnetic properties
- Made with a new developed last technology for extended wearing comfort
- uvex climazone technology ensures optimum wearer comfort
- Breathable, perforated high-tech micro velour upper material
- Distance mesh lining provides optimum breathability
- Suitable for people allergic to chrome, made from synthetic materials
- Virtually seamless design to eliminate pressure points
- Removable comfort insole, antistatic, with moisture control system and additional shock absorption in the heel and at the forefoot
- Soft, padded collar and tongue
- Fulfils ESD requirements: resistance to ground < 35 megohm
- Certified with uvex medicare for individual, orthopaedic inlay soles and individual adjustments

	of the sole unit such as overall increase, inside and outside increase and other solutions																				
Outsole	<ul style="list-style-type: none"> • Multi-layer-shock absorption system using dual density polyurethane for walking comfort • Self-cleaning tread optimised for slip resistance • Free of lacquer wetting inhibitors such as silicones, phthalates, etc. • Ideal shape around the joints for optimal torsion and good flexibility • Joint insert for climbing ladders securely • Pivot point eases turning when standing • High abrasion-resistant PU sections ensure secure stepping and rolling of the foot, which helps prevent accidents 																				
Technical data	<table> <tr> <td>Art.-no.</td> <td>8531.7</td> <td>.8</td> <td>.9</td> <td>.0</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> <td>14</td> </tr> <tr> <td>Standard</td> <td colspan="4">EN ISO 20345:2011 S1 SRC</td> </tr> <tr> <td>Size</td> <td colspan="4">35 – 52</td> </tr> </table>	Art.-no.	8531.7	.8	.9	.0	Width	10	11	12	14	Standard	EN ISO 20345:2011 S1 SRC				Size	35 – 52			
Art.-no.	8531.7	.8	.9	.0																	
Width	10	11	12	14																	
Standard	EN ISO 20345:2011 S1 SRC																				
Size	35 – 52																				
Accessories	<p><i>uvex 1 comfortable climatic insole</i> (article no.: 9534.7-9 + .0)</p> <ul style="list-style-type: none"> • Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones • Ultra breathable and moisture-absorbing materials • Shock absorption zones that assist natural movement • Non-irritating, comfortable surface structure <p><i>Laces</i></p> <ul style="list-style-type: none"> • black (article no.: 9599.909) • Elastic laces (article no.: 9591.000) 																				