

Portrait/Vertical TV Wall Mount - Heavy Duty TV Wall Mount - 40-55" VESA Display (110lb/50kg)-  
Tilting Low Profile Television Digital Signage Mount with Lockable Security Bar

**Product ID:** FPWTLTPORT



This Universal Portrait TV Wall Mount is ideal for customer-facing applications like menu boards or digital signage in hotels requiring the flexibility of portrait / landscape setup. Thanks to its durable steel frame, it can support VESA compatible displays from 40" to 55" and up to 110lb / 50kg in weight. It provides a sleek and professional look thanks to its low profile (3in / 78mm from the wall at the straight angle), and its powder coated finish.

This vertical TV wall mount enables you to adjust the tilting angle by hand (0/+5/+10) using the tilt pin to adjust to the ideal viewing angle. Using the built-in ratchet/lever screw handle this wall mount lets you make micro-height adjustments by hand (range of 10mm) to precisely align your TV when used as part of a multi-display setup (video wall).

The hook-and-mount design of the vertical TV wall mount allow for an easy and fast installation by hanging the TV to the wall mount and securing it using the locking screws. The included long screwdriver has been specially design to make the installation easier.

The portrait TV wall mount provides an extra level of security with the included locking bar, this enables you to lock your TV using a padlock (not included), specially for public setups where you need to leave your equipment unattended.

FPWTLTPORT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

## Features

- **40"-55" PORTRAIT TV WALL MOUNT:** This heavy-duty vertical TV wall mount supports VESA displays from 40 to 55 inches (110lb/50kg); durable tilting steel frame & powder-coated finish; Ideal for menu boards or digital signage in hotels, airports & lobbies
- **ADJUST TILT BY HAND:** 3 different tilting angles (0, +5, +10) which can be adjusted by hand & secured in place using the tilt pin; With a low profile of just 3in from the wall when set at the straight angle (0)
- **EASY INSTALLATION AND LOCKABLE SECURITY:** Flat panel/flat screen TV mount with hook-and-mount design & included long screwdriver (23.6in/60cm long) make for an easy installation; Includes a locking security bar to secure your TV (padlock not incl.)
- **EASY MICRO-HEIGHT ADJUSTMENTS:** Make micro-height adjustments by hand with the built-in ratchet/lever screw handle; Micro-height adjustable with a range of 0.4" (10mm), enables precise alignment of multiple screens
- **COMPATIBILITY:** Universal LCD/LED television mount supports LG, Samsung, Sony, Sharp, others (screws/spacers incl) & VESA bracket hole patterns 200x200, 200x300, 200x400, 300x200, 300x300, 400x400, 400x500, 400x600

---


#### Hardware

Warranty	5 Years
Wallmountable	Yes
Cable Management	No
# of Displays Supported	1
Orientation	Vertical
Minimum Profile from Wall	3.0 in [76.2 mm]
VESA Hole Pattern(s)	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x400 mm
	400x500 mm
	400x600 mm

---

#### Performance

Weight Capacity (Per Display)	110.5 lb [50 kg]
-------------------------------	------------------



Minimum Display Size	40"
Maximum Display Size	55"
Fits Curved Display	No
Video Wall	No
Display Tilt	0 / -5/ -10
Anti-theft	Yes

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	26.8 in [68.0 cm]
Product Width	19.7 in [50.0 cm]
Product Height	3.1 in [78.0 mm]
Weight of Product	9.5 lb [4.3 kg]

---

**Packaging Information**

Package Length	9.4 in [24.0 cm]
Package Width	21.9 in [55.5 cm]
Package Height	3.3 in [83.0 mm]
Shipping (Package) Weight	9.9 lb [4.5 kg]

---

**What's in the Box**

Included in Package	Wall plate
	Display mounting brackets
	Extension brackets
	Security bar
	Extension bracket screws - M6 x 6



Round washers, small

Tilt pins

5mm Hex key

Phillips screwdriver

M5x14 screws

M6x14 screws

M6x30 screws

M8x30 screws

M8x50 screws

Rectangular washers

Short spacers

Long spacers

Mounting screws - ST6.3 x 5.5

Concrete anchors

Round washers, large

---

***\*Product appearance and specifications are subject to change without notice.***

