



1560 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Peli™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Peli cases have survived. Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Strong polyurethane wheels with stainless steel bearings**
- **Watertight, crushproof, and dustproof**
- 2 level Pick N Pluck™ with convoluted lid foam
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Comfortable rubber over-molded top and side handles
- Easy open double-throw latches
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Retractable extension trolley handle
- Stainless steel hardware and padlock protectors
- Peli's legendary lifetime guarantee**
- * Where applicable by law



CONFIGURATIONS



1560
Standard



1564
With Padded Dividers




1560NF
No Foam




1560TP
With TrekPak Divider System



1560WF
With Foam



1560TPL
TrekPak Divider System with
Mesh Lid Organizer



1560PDL
Padded Dividers with Mesh Lid
Organizer

DIMENSIONS

Interior (L×W×D)	19.92 x 14.98" x 9.00 (50.6 x 38 x 22.9 cm)
Exterior (L×W×D)	22.07 x 17.92" x 10.42 (56.1 x 45.5 x 26.5 cm)
Lid Depth	2.00" (5.1 cm)
Bottom Depth	7.00" (17.8 cm)
Total Depth	9" (22.9 cm)
Int Volume	1.55 ft ³ (0.044 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Desert Tan	 Orange	 Yellow
---	--	--	--

WEIGHT

Weight With Foam	20.00 lbs (9.1 kg)
Weight Empty	17.00 lbs (7.7 kg)
Buoyancy	115.00 lbs (52.2 kg)
Master Pack Weight	21.00 lbs (9.5 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	210°F (98.9 °C)

CERTIFICATIONS

IP67	
Def Stan 81-41	

OTHER

Wheels	2
Extendable Handle	yes
Master Pack	1
Nameplate	yes
Military	yes

ACCESSORIES

				
0343 Replacement O-ring	1561 4 pc. Replacement Foam Set	1565 Padded Divider Set	1569 Lid Organizer	1560EUTP TrekPak Case Divider Kit
				
1560TPKIT TrekPak Case Divider Kit	1560TPDIV Extra TrekPak Dividers	1507 Quick Mounts - set of 4	1506TSA TSA Lock	1500D Desiccant Silica Gel



1560MP
EZ-Click™ MOLLE Panel

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com

Document created on 05-09-25