

Torq Chem X

360 degree cut and chemical resistant pvc / nitrile impact gauntlet

This PVC/Nitrile cut and impact resistant gauntlet features surprisingly responsive impact protection without sacrificing grip or chemical protection.

Features

- ▲ 15g aramid / steel blend ensures high cut protection
- ▲ Mix of PVC and nitrile which provides the benefits of both polymers
- ▲ Palm made of a foam PVC/Nitrile ensures grip in dry, wet, oily and chemical handling applications
- ▲ Excellent protection against mud, hydrocarbons, oil, water and many chemicals
- ▲ Cushioned impact coverage balances dexterity with protection
- ▲ 350mm length for extended cuff protection



Certifications

CAT III	IMPACT	EN 374-1: 2016/ Type A	EN 388:2016 + A1:2018	EN 374-5: 2016	ANSI 105:2016
	Level 2	A, J, K, L, M, N, O, P, T	4X41EP	Micro Organisms	A5 X 4

Suitable industries & applications

Industries

- | | |
|-----------------|--------------------|
| ▲ Chemicals | ▲ Maritime |
| ▲ Construction | ▲ Oil and Gas |
| ▲ Manufacturing | ▲ Steel and Metals |

Applications

- | | |
|---------------------------------------|---------------------------------------|
| ▲ Civil Engineering | ▲ Metal Fabrication Work |
| ▲ Demolition | ▲ Transportation of Fuels |
| ▲ Fossil Fuel Extraction and Refining | ▲ Vessel Construction and Maintenance |

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Torq Chem X

360 degree cut and chemical resistant pvc / nitrile impact gauntlet




Product information

Materials	Liner:	15 Gauge Para-Aramid, Steel Fibre
	Coating:	PVC, Nitrile
Colour	Red / Black	
Length	350mm	
Cuff Style	Gauntlet	

Ordering information

S	SKG00093HD	Items per Pack 6 x Pairs
M	SKG00093HF	
L	SKG00093HH	Items per Case 30 x Pairs
XL	SKG00093HJ	
XXL	SKG00093HL	

Additional information

<p>Certification legend</p>  <p>or click here</p>	<p>Declaration of conformity</p>  <p>or click here</p>	<p>View product online</p>  <p>or click here</p>
--	---	---

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747