



SETRON, cylindrical fuse link, 10x85 mm, 16 A, gPV, Un DC: 1500 V

Figure similar


| Model                                    |       |                          |
|------------------------------------------|-------|--------------------------|
| product brand name                       |       | SETRON                   |
| product designation                      |       | Cylindrical fuse link    |
| General technical data                   |       |                          |
| operating class of the fuse link         |       | gPV                      |
| type of voltage of the operating voltage |       | DC                       |
| supply voltage at DC                     |       | 1 500 V                  |
| Main circuit                             |       |                          |
| operational current rated value          |       | 16 A                     |
| Product details                          |       |                          |
| product component striker                |       | No                       |
| Mechanical Design                        |       |                          |
| mounting position                        |       | Any, preferably vertical |
| net weight                               |       | 17 g                     |
| Approvals Certificates                   |       |                          |
| General Product Approval                 | other | Environment              |



[Confirmation](#)

[Environmental Con-  
firmations](#)

| Further information                                                                             |                                                                                                                                                                       |
|-------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Information on the packaging                                                                    | <a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a>                               |
| Information- and Downloadcenter (Catalogs, Brochures,...)                                       | <a href="http://www.siemens.com/lowvoltage/catalogs">http://www.siemens.com/lowvoltage/catalogs</a>                                                                   |
| Industry Mall (Online ordering system)                                                          | <a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6605-4">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6605-4</a> |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,...)                              | <a href="https://support.industry.siemens.com/cs/ww/en/ps/3NW6605-4">https://support.industry.siemens.com/cs/ww/en/ps/3NW6605-4</a>                                   |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) | <a href="http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6605-4">http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6605-4</a>                 |
| CAX-Online-Generator                                                                            | <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>                                                                                                   |
| Tender specifications                                                                           | <a href="http://www.siemens.com/specifications">http://www.siemens.com/specifications</a>                                                                             |



last modified:

4/11/2025 

