

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Wheeled
- Height Adjustable
- Back Adjustable
- Seat Adjustable
- Headrest Adjustable

RS PRO ESD Superior 2

RS Stock No.: 0665656



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The Superior 2 ESD Chair is an advanced solution designed for environments where electrostatic discharge (ESD) protection is critical. By combining excellent ergonomics with modern design, it ensures a high level of comfort and safety, making it ideal for demanding workspaces.

Product Features:

- ✓ **Ergonomic seat and backrest with high-resilience foam** – adapt to the shape of the body, providing exceptional comfort during long hours
- ✓ **Adjustable seat height and depth, as well as backrest height and tilt angle** – for full ergonomic personalization
- ✓ **Adjustable headrest** – allows tilt and height adjustment for enhanced support of the neck and head
- ✓ **Sturdy aluminium five-star base** – ensures long-lasting durability and excellent stability under heavy use
- ✓ **Wear-resistant, ESD-safe fabric** – aids in the safe dissipation of electrostatic charges
- ✓ **Conductive castors (0665661)** – rubber-coated to protect floor surfaces from scratches and ensure smooth movement
- ✓ **Easy to maintain** – available in fabric options that are resistant to dirt and simple to clean

Applications:

The Superior 2 ESD Chair is a perfect choice for production lines, and technical service centers where reliable ESD control is essential. Thanks to its ergonomic design and headrest, it is also well-suited for modern office spaces, offering comfort and support during long work sessions. Our products are widely used in industries such as electronics, automotive, general manufacturing, medical, pharmaceutical, and defense.

General Specifications

TOTAL HEIGHT (mm)	840-1170
TOTAL WIDTH (mm)	660
WEIGHT (kg)	11,8
MAX LOAD CAPACITY (kg)	120 (up to 200 kg with a special gas lift)
HEIGHT ADJUSTMENT RANGE (mm)	440-495mm
SEAT DIMENSIONS (mm)	450 x 440
BACKREST DIMENSIONS (mm)	310 x 400
ESD	YES
COLOUR	BLACK
MATERIAL	POLYURETHANE
BASE MATERIAL	ALUMINIUM
CASTORS	CONDUCTIVE, RUBBER-COATED TO PREVENT SCRATCHING
RESISTANCE GROUNDING (0hm)	10 ⁶ – 10 ⁸

Approvals

Chair compliance with standards	PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007
Fabric compliance with standards	PN-EN 1021-1:2014-12, PN-EN 1021-2:2014-12

Similar Products

Stock No.	Brand	Product Name
0665655	RS PRO	ESD SUPERIOR 1 chair, seat height adjustment 420-490mm

Accessories

Stock No.	Brand	Product Name
0665661	RS PRO	ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**)
0665662	RS PRO	ESD metal castor, diameter 50mm
0665664	RS PRO	ESD glides
0665665	RS PRO	ESD footrest
0665667	RS PRO	ESD PU armrests, dedicated to premium models (0665655, 0665656)
0665669	RS PRO	ESD armrests, black steel + antistatic PU covers, dedicated to premium models (0665655, 0665656)
		armrests with height adjustment, black steel + antistatic PU covers, dedicated to premium models (0665655, 0665656)

Electrical Specifications