


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SCHEDULE

TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
2176777-1	TLMQ2BDR010FTD	TLMQ 1206 1W R010 1% 50PPM 5K RL	PRODUCTION
2176777-2	TLMQ2BDR011FTD	TLMQ 1206 1W R011 1% 50PPM 5K RL	PRODUCTION
2176777-3	TLMQ2BDR012FTD	TLMQ 1206 1W R012 1% 50PPM 5K RL	PRODUCTION
2176777-4	TLMQ2BDR013FTD	TLMQ 1206 1W R013 1% 50PPM 5K RL	PRODUCTION
2176777-5	TLMQ2BDR015FTD	TLMQ 1206 1W R015 1% 50PPM 5K RL	PRODUCTION
2176777-6	TLMQ2BDR016FTD	TLMQ 1206 1W R016 1% 50PPM 5K RL	PRODUCTION
2176777-7	TLMQ2BDR018FTD	TLMQ 1206 1W R018 1% 50PPM 5K RL	PRODUCTION
2176777-8	TLMQ2BDR020FTD	TLMQ 1206 1W R020 1% 50PPM 5K RL	PRODUCTION
2176777-9	TLMQ2BDR022FTD	TLMQ 1206 1W R022 1% 50PPM 5K RL	PRODUCTION
1-2176777-0	TLMQ2BDR024FTD	TLMQ 1206 1W R024 1% 50PPM 5K RL	PRODUCTION
1-2176777-1	TLMQ2BDR027FTD	TLMQ 1206 1W R027 1% 50PPM 5K RL	PRODUCTION
1-2176777-2	TLMQ2BDR030FTD	TLMQ 1206 1W R030 1% 50PPM 5K RL	PRODUCTION
1-2176777-3	TLMQ2BDR033FTD	TLMQ 1206 1W R033 1% 50PPM 5K RL	PRODUCTION
1-2176777-4	TLMQ2BDR036FTD	TLMQ 1206 1W R036 1% 50PPM 5K RL	PRODUCTION
1-2176777-5	TLMQ2BDR039FTD	TLMQ 1206 1W R039 1% 50PPM 5K RL	PRODUCTION
1-2176777-6	TLMQ2BDR043FTD	TLMQ 1206 1W R043 1% 50PPM 5K RL	PRODUCTION
1-2176777-7	TLMQ2BDR047FTD	TLMQ 1206 1W R047 1% 50PPM 5K RL	PRODUCTION
1-2176777-8	TLMQ2BDR051FTD	TLMQ 1206 1W R051 1% 50PPM 5K RL	PRODUCTION
1-2176777-9	TLMQ2BDR056FTD	TLMQ 1206 1W R056 1% 50PPM 5K RL	PRODUCTION
2-2176777-0	TLMQ2BDR062FTD	TLMQ 1206 1W R062 1% 50PPM 5K RL	PRODUCTION
2-2176777-1	TLMQ2BDR068FTD	TLMQ 1206 1W R068 1% 50PPM 5K RL	PRODUCTION
2-2176777-2	TLMQ2BDR075FTD	TLMQ 1206 1W R075 1% 50PPM 5K RL	PRODUCTION
2-2176777-3	TLMQ2BDR082FTD	TLMQ 1206 1W R082 1% 50PPM 5K RL	PRODUCTION
2-2176777-4	TLMQ2BDR091FTD	TLMQ 1206 1W R091 1% 50PPM 5K RL	PRODUCTION
2-2176777-5	TLMQ2BDR10FTD	TLMQ 1206 1W R10 1% 50PPM 5K RL	PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAMESHA L S 19FEB2025	 TE Connectivity			
		CHK TRACY G 19FEB2025				
DIMENSIONS: mm		APVD TRACY G 19FEB2025	NAME SMD CURRENT SENSE METAL CHIP RESISTOR TYPE TLMQ 1206 SERIES			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2176777	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 2	REV BA	