

# Industrials chargers to 300 mA at 25A - 6V 12V 24V

Standby application / Floating and Cyclic - Automatic chargers with microprocessor for VRLA batteries  
Motorcycles batteries / Power supplies-Chargers


Ref.	Type of charger	Voltage (V)	Current max. (A)	Sized for batteries	Dimensions (mm)			Weight (Kg)	Battery connectors
					L	D	H		
1	YCP03A6	6	0,3	de 1,2Ah à 3Ah	102	61	47	0,41	A
2	YCP06A6	6	0,6	de 2,4Ah à 6Ah	102	61	47	0,41	A
3	YCPA6	6	1	de 3,4Ah à 6 Ah	102	61	47	0,41	A
4	YCP03A12	12	0,3	de 1,2Ah à 3Ah	102	61	47	0,41	A
5	YCP06A12	12	0,6	de 2,4Ah à 6 Ah	102	61	47	0,41	A
6	YCP03A24	24	0,3	de 1,2 Ah à 6 Ah	102	61	47	0,41	A
7	YCP1.5A6	6	1,5	de 6Ah à 15Ah	130	90	65	1,3	B
8	YCP2A6	6	2	de 8Ah à 20Ah	130	90	65	1,3	B
9	YCP1A12	12	1	de 4Ah à 10Ah	130	90	65	1,3	B
10	YCP1.5A12	12	1,5	de 6Ah à 15Ah	130	90	65	1,3	B
11	YCP2A12	12	2	de 8Ah à 20Ah	130	90	65	1,3	B
12	YCP08A24N	24	0,8	de 3,2Ah à 8 Ah	130	90	65	1,3	E
13	YCP1A24	24	1	de 4Ah à 10Ah	130	90	65	1,3	B
14	YCP3A12	12	3	de 12Ah à 30Ah	143	103	91	1,9	B
15	YCP4A12	12	4	de 16Ah à 40Ah	143	103	91	1,9	B
16	YCP2A24	24	2	de 8Ah à 20Ah	143	103	91	1,9	B
17	YCP6A12	12	6	de 24Ah à 60Ah	240	140	85	2,1	B
18	YCP8A12	12	8	de 32Ah à 80Ah	240	140	85	2,1	B
19	YCP10A12	12	10	de 40Ah à 100Ah	240	140	85	2,1	B
20	YCP12A12	12	12	de 48Ah à 120Ah	240	140	85	2,1	B
21	YCP20A12	12	20	de 80Ah à 100Ah	240	140	85	2,1	B
22	YCP4A24	24	4	de 16Ah à 40Ah	240	140	85	2,1	B
23	YCP6A24	24	6	de 24Ah à 60Ah	240	140	85	2,1	B
24	YCP8A24	24	8	de 32Ah à 80Ah	240	140	85	2,1	B
25	YCP10A24	24	10	de 40Ah à 100Ah	240	140	85	2,1	B
26	YCP12A24	24	12	de 48Ah à 120Ah	240	140	85	2,1	B
27	MC06A6	6	0,6	de 2,4Ah à 6Ah	102	61	47	0,41	B C D
28	MC06A12	12	0,6	de 2,4Ah à 6Ah	102	61	47	0,41	B C D
29	PS12A12	12	12	de 48Ah à 120Ah	143	103	91	1,9	FREE
30	PS15A12	12	15	de 60Ah à 150Ah	143	103	91	1,9	FREE
31	PS20A12	12	20	de 80Ah à 200Ah	143	103	91	1,9	FREE
32	PS20A12	12	25	de 100Ah à 250Ah	143	103	91	1,9	FREE

YCP : VRLA batteries    MC : Motorcycles batteries    PS : Power supplies-Chargers for on board applications

In compliance with the standards : BS3456, IEC335, ULI236, EN60335, CE in ENB5008-1



## Battery connectors




6,35 female connectors with boots



Crocodile clip



Double connector



Double connector with fuse



Connector 4 pins

# Yu-Power chargers

Ref.	Type of charger	Voltage (V)	Current max. (A)	Sized for batteries	Dimensions (mm)			Weight (Kg)	Battery connectors
					L	D	H		
33	YPC09A12MC	12	0,9	Motos <20Ah	95,5	66	87,5	0,51	G
34	YPC2A6	6	2	6 à 20 Ah	140	65	42	0,45	G
35	YPC2A12	12	2	6 à 20 Ah	140	65	42	0,45	G
36	YPC4A12	12	4	12 à 40 Ah	164	85	55	0,62	F
37	YPC8A12	12	8	30 à 100 Ah	190	92	55	0,86	F
38	YPC4A24	24	4	12 à 40 Ah	190	82	55	0,86	F
39	YPCTESTMC	12	Testeur	Motos	45	20	13	0,01	-



Torbury to clips adaptor



Motorcycle plug to clips adaptor



Torbury to T-bar golf caddy adaptor



Motorcycle plug to ring connectors with fuse

