

HyFlex® 11-616 11-618 11-619

MECHANICAL PROTECTION

 MULTI-PURPOSE

 LIGHT

STYLE #	CONSTRUCTION	GAUGE	LINER MATERIAL	COATING MATERIAL	FINISHING	CUFF STYLE	COLOUR	EN SIZE	LENGTH MM	PACKAGING
11-618	Knitted	18	Nylon	Polyurethane	Palm coated	Knitwrist	Black and dark blue	6, 7, 8, 9, 10, 11	195 - 245	12 pairs in a bag, 12 bags in a carton
11-616	Knitted	18	Nylon	Polyurethane	Palm coated	Knitwrist	Black and green/blue	6, 7, 8, 9, 10, 11	195 - 245	12 pairs in a bag, 12 bags in a carton
11-619	Knitted	18	Nylon	Polyurethane	Palm coated	Knitwrist	White	6, 7, 8, 9, 10, 11	195 - 245	12 pairs in a bag, 12 bags in a carton



The next generation glove in comfort, dexterity and flexibility

PRIMARY INDUSTRIES



IDEAL APPLICATIONS

- Light assembly applications requiring a high degree of precision
- Final assembly, airco, electrical engines, wire harness assembly, adjusters work
- White goods and electrical goods
- Cosmetics/plastics (also packaging stage)
- Finishing works
- Picking and fitting small pieces (bearings, springs...)

DESCRIPTION

- Almost a second skin, this very thin glove offers outstanding comfort, fit and sensitivity for the most delicate handling.
- 18-gauge knitting technology allows this glove to be ultra-thin yet tough.
- Designed for a wide range of lightweight applications in dry or slightly oily environments, it is ideal for workers who need a higher level of fit, touch and precision than that offered by their current gloves.
- Also ideal for applications where cotton gloves or no gloves at all are used despite the risk of scrapes, blisters and minor injuries.
- In addition, the 11-618 and 11-616 dark liners are well-suited for environments that present a certain degree of dirt.
- The white color is ideal for clean environments / dirt sensitive applications.

REMARKS

- Fit for special purpose

11-618:3121
11-616:2121
11-619:2121



CATEGORY II

Print date: 07-05-2014

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

http://www.ansell.eu • E-mail info@ansell.eu