

CTK110NEU

Professional Tools Set CTK110NEU

The Set includes 110 pieces in high-quality Chrome-Vanadium.
All pieces are fixed in a handy plastic case.



Code No.	Description	EAN
CTK110NEU	Professional Tool Set, 110 pieces	037103110633

Content CTK110NEU

	Sockets matte chromed
	Pliers ChromeVanadium, mirror finish, with cushion grip
1	1/2" Quick Release Ratcheting Drive, 72-tooth, with cushion grip, CrV
1	1/2" Extension 125 mm, CrV
1	1/2" Universal Joint, CrV
15	1/2" Sockets 10, 11, 12, 13, 14, 15, 17, 18, 19, 20, 21, 22, 23, 24, 27 mm, CrV, 6 pt
1	1/2" Sliding T-Handle / Extension 250 mm, CrV
1	1/2" Spark Plug Socket 16 mm, CrV
1	1/2" Spark Plug Socket 21 mm, CrV
1	1/4" Quick Release Ratcheting Drive, 72-tooth, with cushion grip, CrV
2	1/4" Extension 50 mm and 100 mm, CrV
1	1/4" Universal Joint, CrV
1	1/4" Flexible Extension 150 mm, CrV
11	1/4" Sockets 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14 mm, CrV, 6 pt
11	Combination Wrenches 8, 9, 10, 11, 12, 13, 14, 15, 17, 18, 19 mm, CrV
2	Screwdriver, Slotted 6,5 x 100 mm and 5,5 x 75 mm
2	Screwdriver, Phillips #1x 75 mm and #2 x 100 mm
1	Magnetic Bit Driver for 1/4"/25mm Bits with left-/right-Drive
40	Screwdriver Bits 1/4"/25mm long
4	Bit Holders
8	Hex Keys 1,5 / 2 / 2,5 / 3 / 4 / 5 / 5,5 / 6 mm
1	Hex Key Holder
1	Long Nose Plier w/Spring 8"/200 mm , CrV, with co-molded handles
1	Diagonal Cutting Plier w/spring 6"/150 mm, CrV, with co-molded handles
1	Tongue & Groove Plier 7"/175 mm, CrV, with co-molded handles
1	Robust Plastic Case with coloured display box

For further information please contact:

Apex Tool Group B.V.
 Phileas Foggstraat 16
 7821 AK Emmen
 The Netherlands

Tel.: +31 (0) 591 667500
 Fax: +31 (0) 591 667595
 cs.emmen@apextoolgroup.com

