



Lithium-ion Cordless Two-Speed Drill/Driver

EasyDrill 1200

Small, lightweight, powerful –
Cordless power with good value
for money

[Go to product](#)



Key product features

- Syneon Chip: Intelligent control of the energy for optimum power and maximum endurance
- No memory effect, no self-discharge: Always ready to use thanks to lithium-ion technology
- Compact design thanks to lithium-ion technology

Other product advantages

- Bosch Electronic speed control: “accelerate” from 0 – max. using the trigger switch
- High-performance planetary gearbox: superior lifetime, best power transfer, high running smoothness
- PowerLight – thanks to the built-in LED, your workpiece is always well lit and clearly visible
- Torque preselection with 15 torque settings plus a drill setting – optimum power for every application

Comes complete with

- Charger AL 1110 CV
- Carrying case 2.1
- Double screwdriver bit
- 1 battery pack PBA 12V 1.5Ah O-A

Part number: 06039A2172

EAN code: 4053423201352



Lithium-ion Cordless Two-Speed Drill/Driver

EasyDrill 1200

Technical data

Battery voltage: 12 V

Battery capacity: 1,5 Ah

No-load speed (1st gear / 2nd gear): 0 – 450 / 1.650 rpm

No-load speed: 0 – 1.650 rpm

Max. torque: 20 Nm

Max. torque for soft/hard screw. applications: 11 / 20 Nm

Torque settings: 15 + 1

Drill chuck: Keyless chuck

Machine weight with battery: 1 kg

Screw diameter

Screw diameter up to: 6 mm

Drilling diameter

Drilling diameter in steel: 6 mm

Drilling diameter in wood: 20 mm

Noise / vibration information

Measured values determined according to EN 60745.
Total vibration values (vector sum of three directions).

Drilling in metal

Vibration emission value ah: 2.5 m/s²

Uncertainty K: 1.5 m/s²

Screwdriving

Vibration emission value ah: 2.5 m/s²

Uncertainty K: 1.5 m/s²

The A-rated noise level of the power tool is typically as follows: Sound pressure level 66 dB(A); Sound power level 77 dB(A). Uncertainty K= 3 dB.

Functions



Battery voltage

12 volts



Battery runtime

Screwdriving performance with one battery charge



Area of application

Screwdriving / drilling

Functions

12 Volt

Lithium-ion technology

Bosch Electronic Cell Protection (ECP)

2-speed gearbox

Application: screwdriving / drilling

Softgrip

Integrated work light

Bosch Electronic

Right-hand/left-hand rotation

Forward/reverse indicator