

Features

- Delivers fast, efficient cutting through both wood and metal.
- Manufactured from medium-thick 1.25mm gauge M2 High Speed Steel, it delivers the perfect balance between speed, flexibility, and stability for demanding applications.
- Designed to cut soft nails, mild steel, and non-ferrous metal components embedded in wood, the 225mm blade length provides an impressive 175mm cutting capacity.

Reciprocating Saw Blade –Wood & Metal 225 x 19 x 1.25mm –Coarse Cut

RS Stock No.: 0757832



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Reciprocating Saw Blade

0757832 Wood and Metal Reciprocating Saw Blade delivers fast, efficient cutting through both wood and metal. Manufactured from medium thick 1.25mm gauge M2 High Speed Steel, it delivers the perfect balance between speed, flexibility, and stability for demanding applications. Designed to cut soft nails, mild steel, and non-ferrous metal components embedded in wood, the 225mm blade length provides an impressive 175mm cutting capacity.

- *Manufactured with D6A Shock-Resisting Tool Steel & M2 High Speed Steel Teeth*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Wood With Nails, Wooden Pallets & Pipes*
- *Supplied in 5pc Packs*

General Specifications

Tooth Design	Side Set, Milled
Type	Reciprocating Saw Blade
Teeth Spacing	4.0mm
TPI	6
Thickness	1.25mm
Max Cut Depth	175mm
Cut Type	Fast Cutting
Blade Material	M2 High Speed Steel
Body Material	D6A Shock-Resisting Tool Steel
Fitting	S-Shank 1/2"
Length	225mm
Width	19mm

Stock No.	Cut Type	Thickness	Length	Width
XXX-XXXX 0757831	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757832	Coarse Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757833	Fast Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757834	Coarse Cutting	1.25mm	300mm	19mm

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Cut Type	Thickness	Length	Width
XXX-XXXX 0757831	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757832	RS PRO	Reciprocating Saw Blade	Coarse Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757833	RS PRO	Reciprocating Saw Blade	Fast Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757834	RS PRO	Reciprocating Saw Blade	Coarse Cutting	1.25mm	300mm	19mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories