


IDXPERT™ Electrical Identification Labels



Wire and Cable Markers – PermaSleeve™ Sleeves

B-342 Heat-Shrinkable White and Yellow Polyolefin, 3:1 shrink ratio


Diagram	Order Reference	Labels Per Cartridge	Dimensions		Colour
			A (mm)	B (mm)	
12-6 Gauge dia 3.20 - 8.10 mm					
■	XPS-375-1	100	25.78	16.38	BK on WT
■	XPS-375-CONT	Cont.	16.38	2.44 m	BK on WT
16-10 Gauge dia 2.40 - 5.50 mm					
■	XPS-250-1	100	25.78	11.15	BK on WT
■	XPS-250-CONT	Cont.	11.15	3.65 m	BK on WT
■	XPS-250-CONT-YL-BK	Cont.	11.15	3.65 m	BK on YL
18-12 Gauge dia 1.60 - 3.80 mm					
■	XPS-187-1	100	25.78	8.50	BK on WT
■	XPS-187-CONT	Cont.	8.50	2.44 m	BK on WT
■	XPS-187-CONT-YL-BK	Cont.	8.50	2.44 m	BK on YL
22-16 Gauge dia 1.20 - 2.80 mm					
■	XPS-125-1	100	25.78	5.96	BK on WT
■	XPS-125-CONT	Cont.	5.96	2.44 m	BK on WT
■	XPS-125-CONT-YL-BK	Cont.	5.96	2.44 m	BK on YL

*Approx based on NEC for THHN wire.

Terminal Block Markers

B-498 Repositionable White Vinyl Cloth

Diagram	Order Reference	Labels Per Cartridge	Label dimensions		Colour
			A mm	B m	
●	XC-240-498	Cont.	6.10	6.10 m	BK on WT
●	XC-318-498	Cont.	8.07	6.10 m	BK on WT
●	XC-375-498	Cont.	9.53	6.10 m	BK on WT



IDXPERT™ Electrical Identification Labels

Cable Markers

When you are looking for cable markers with extreme durability, the Laminat range of carriers and tags is the solution. There are two types of Laminat cable markers: Laminat™ Carriers (B-7644), Laminat™ Tags (B-7645)

B-7644 Laminat™ Carriers

Laminat™ Carriers come with a strip to laminate text labels. The carrier is fixed with two cable ties directly on the cables or wires. This dependable marking system enables you to permanently mark cables and wires.

The Laminat™ Carriers can be used for any type of cable identification where permanency of the legend is crucial. Follow these steps to mount the label onto the Laminat™ carrier:



1) Pull the protective foil backwards




2) Place the label in the middle leaving space for sealing on all four sides of the label.



3) Seal the carrier by placing a finger on the foil and pushing forward, thus rolling over the foil and rolling off the silicon liner.




4) Always feed the cable ties from the top, thus bending down the Laminat™ carrier along the cable.



Order Reference	Markers Per Box	Material	Colour	Dimensions		Seal-Up Area		Labels /Tapes Recommended
				Width A (mm)	Height B (mm)	C (mm)	D (mm)	
LC-65x13-B7644	100	Polypropylene	Yellow	65.00	13.00	45.00	9.00	XC-236-580-YL-BK
LC-71x9-B7644	100	Polypropylene	Yellow	71.00	9.00	45.00	9.00	XC-236-580-YL-BK
LC-103x15-B7644	100	Polypropylene	Yellow	103.00	15.00	55.00	15.00	XC-354-580-YL-BK
LC-128x15-B7644	100	Polypropylene	Yellow	128.00	15.00	80.00	15.00	XC-354-580-YL-BK
LC-178x15-B7644	50	Polypropylene	Yellow	178.00	15.00	130.00	15.00	XC-354-580-YL-BK

B-7645 Laminat™ Tags

The Laminat™ Tags (Manilla tags) are ideal for identification of material in tough environments including valves, instruments, motors and other industrial components. The tags are available in two versions: with and without stainless steel reinforcement rings.



Order Reference	Markers Per Box	Material	Colour	Dimensions		Seal-Up Area		Labels /Tapes Recommended
				Width A (mm)	Height B (mm)	C (mm)	D (mm)	
LT-59x25-B7645	50		Yellow	59.00	25.00	43.00	25.00	XC-354-580-YL-BK
LT-59x25-B7645-WR	50	Reinforced	Yellow	59.00	25.00	43.00	25.00	XC-354-580-YL-BK
LT-150x25-B7645	50		Yellow	150.00	25.00	135.00	25.00	XC-500-580-CL-BK
LT-150x25-B7645-WR	50	Reinforced	Yellow	150.00	25.00	135.00	25.00	XC-500-580-CL-BK

Labels Specifically Designed to Fit The Laminat Carriers and Tags

B-580 White and Yellow Indoor/Outdoor Vinyl




Diagram	Order Reference	Labels Per Cartridge	Label dimensions		Colour
			A (mm)	B (m)	
○	XC-236-580-WT-BK	Cont.	6.00	9.14	BK on WT
○	XC-236-580-YL-BK	Cont.	6.00	9.14	BK on YL
○	XC-354-580-WT-BK	Cont.	9.00	9.14	BK on WT
○	XC-354-580-YL-BK	Cont.	9.00	9.14	BK on YL
○	XC-500-580-CL-BK	Cont.	12.70	7.62	BK on CL