

A-INL-M25-P-BK - Counter nut



1411216

<https://www.phoenixcontact.com/gb/products/1411216>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M25 x 1.5, color: jet black



Commercial data

Item number	1411216
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 686 (C-2-2019)
GTIN	4046356923484
Weight per piece (including packing)	3.92 g
Weight per piece (excluding packing)	3.8 g
Customs tariff number	39269097
Country of origin	TR

A-INL-M25-P-BK - Counter nut

1411216


<https://www.phoenixcontact.com/gb/products/1411216>

Technical data

Product properties

Product type	Flat nut
Thread type	M25

Dimensions

Dimensional drawing	
Length	6 mm
Diameter	25 mm
Connecting thread diameter	25 mm
Wrench size, counter nut	32 mm
Hexagon angular dimension	35 mm
Thread type connection side	M25 x 1.5
Thread pitch	1.5 mm

Material specifications

Material	PA
Flammability rating according to UL 94	V2

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

A-INL-M25-P-BK - Counter nut


1411216

<https://www.phoenixcontact.com/gb/products/1411216>



Drawings

Dimensional drawing



A-INL-M25-P-BK - Counter nut



1411216

<https://www.phoenixcontact.com/gb/products/1411216>

Classifications

ECLASS

ECLASS-13.0	27140807
-------------	----------

ETIM

ETIM 9.0	EC000879
----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-M25-P-BK - Counter nut



1411216
<https://www.phoenixcontact.com/gb/products/1411216>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk