

14052 DZH-40-25-PPV-A Flat cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	108707	DZH- 40-PPV-A Set of wearing parts	Spare parts: 2, 8, 11, 17, 18, 22, 23	1	PC
1	203968	DIN 439-B-M12X1,25-04 Hex nut		1	PC
2	232275	WIFC2-16X26X10,7-TPE-U Wiper seal	Grease using during assembly. See position 22	1	PC
3		SINT-B50 16X22X20 Cylinder bearing	Not available separately, see position 9	1	PC
4		DZH-40-PPV Bearing cap module	Not available separately, see position 9	1	PC
5		B-6X1-N-NBR75 O-ring ISO3601	Not available separately, see position 9+21	2	PC
6		RG2 3X8X11.6X5 adjusting screw	Not available separately, see position 9+21	2	PC
7		RG2-M5X0,5-8-6,3 Threaded sleeve	Not available separately, see position 9+21	2	PC
8		DIFC1-20X28X7,8-TPE-U Buffer seal	Not available separately, see position 9+21+999 Grease using during assembly. See position 22	2	PC
9	760699	DZH-40-PPV:SP Bearing cap module		1	PC
10	241994	M6X50 DZH- 40 flange screw	Use locking compound. See position 23 Tightening torque 11 Nm / 8.1 lbf ft	8	PC
11		B-42X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 22	2	PC
12		ARA-16-X0067,5-A1 Piston rod	Not available separately, see position 16	1	PC
13		DZH-40-PPV-A Piston	Not available separately, see position 16	1	PC
14		6,1X7,5 Magnet	Not available separately, see position 16	1	PC
15		DZH-40-PPV-A Piston	Not available separately, see position 16	1	PC
16	106954	DZH-40-X-PPV-A Piston rod module	When ordering please specify the stroke (see type plate)	1	PC
17		LEFO1-52X31X7-TPE-U Lip seal	Not available separately, see position A Grease using during assembly. See position 22	2	PC
18		DZH-40-PPV-A Guiding band	Not available separately, see position A Grease using during assembly. See position 22	2	PC
19		DZH-40-... Cylinder barrel	Not available Grease using during assembly. See position 22	1	PC
20		DZH-40-PPV:CO End cap	Not available separately, see position 21	1	PC
21	8217553	DZH-40-PPV:SP End cap module		1	PC
22	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		1	PC
23	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC