



INSULATED SOCKET 1000V 1/2 6 PANS

ZSH-...

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:54:09





DESCRIPTION

INSULATED SOCKET 1000V 1/2 6 PANS

Manual sockets designed for use with a standard or mechanical-locking ratchet wrench. Long sockets specially suited for places that are difficult to access such as wells and long threads. Made of Chrome Vanadium steel. The socket has 4 ogive-type housings inside the female square, offering an efficient and secure place for the ratchet's crimped ball, thus ensuring reliable assembly fastening (up to 500 Newtons pull-out resistance). Presence of a collar to provide optimum electrical protection during use with a ratchet or an extension.

SPECIFIC DATA

SAM Outillage


10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:54:09





Sales reference	Weight (kg)	Width (mm)	Length (mm)	Height (mm)	Guarantee
ZSH-8	0.06	25	25	54	O
ZSH-23	0.120	35	35	55	O
ZSH-22	0.12	35	35	55	O
ZSH-29	0.17	41.1	45	45	O
ZSH-12	0.08	24	24	52	O
ZSH-17	0.08	27	27	55	O
ZSH-24	0.14	34.9	40	40	O
ZSH-28	0.17	39.9	45	45	O
ZSH-13	0.08	27	27	56	O
ZSH-16	0.08	27	27	56	O
ZSH-27	0.17	38	45	45	O
ZSH-14	0.08	24	24	52	O
ZSH-25	0.14	36.1	40	40	O
ZSH-26	0.17	37.2	42	42	O
ZSH-11	0.06	26	26	55	O

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:54:09



ZSH-18	0.08	29	29	55	O
ZSH-20	0.1	33	33	55	O
ZSH-21	0.1	34	34	55	O
ZSH-32	0.26	44	45	45	O
ZSH-9	0.06	25	25	53	O
ZSH-15	0.08	26	26	54	O
ZSH-30	0.19	42	45	45	O
ZSH-19	0.1	30	30	55	O
ZSH-31	0.24	43.6	45	45	O
ZSH-10	0.06	24	24	52	O

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:54:09

