


CD-HF 40X80 BU - Cable duct

3240592

<https://www.phoenixcontact.com/gb/products/3240592>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, blue, halogen-free, comprising upper part and mounting base, width: 40 mm, height: 80 mm, length: 2000 mm

Commercial data

Item number	3240592
Packing unit	16 pc
Minimum order quantity	16 pc
Sales key	BE7442
Product key	BE7442
Catalog page	Page 579 (C-3-2019)
GTIN	4046356630108
Weight per piece (including packing)	901 g
Weight per piece (excluding packing)	768 g
Customs tariff number	39259020
Country of origin	DE

CD-HF 40X80 BU - Cable duct

3240592

<https://www.phoenixcontact.com/gb/products/3240592>



Technical data

Product properties

Product type	Wiring duct
--------------	-------------

Dimensions

Width	40 mm
Height	80 mm
Length	2000 mm

Material specifications

Color	blue (RAL 5015)
Material	PC/ABS
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1, HL 2, HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1, HL 2, HL 3
Components	halogen-free

Cable/line

Halogen-free	yes
--------------	-----

Mechanical properties

Usage cross-section	2671 mm ² (100 %)
Number of cables at 60% filling volume	96 (2.5 mm ² Ø 3.4 mm)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

CD-HF 40X80 BU - Cable duct



3240592

<https://www.phoenixcontact.com/gb/products/3240592>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240592>



CSA

Approval ID: 80202282



VDE approval of drawings

Approval ID: 40058453

DNV

Approval ID: TAE00004VN



UL Recognized

Approval ID: E328576

CD-HF 40X80 BU - Cable duct



3240592

<https://www.phoenixcontact.com/gb/products/3240592>

Classifications

ECLASS

ECLASS-13.0	27400703
-------------	----------

ETIM

ETIM 9.0	EC000012
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD-HF 40X80 BU - Cable duct



3240592

<https://www.phoenixcontact.com/gb/products/3240592>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk