



## MATERIAL FACT SHEET

### 719998 FX5S-60MT/DSS

#### General Data

Product Hierarchy	IAD21705
	Compact PLC
	FX5S CPU
Ext. Material Group	10 STANDARD ITEM
ABC Indicator	B (Limited Availability from Stock)

e-shop: <https://emea.mitsubishielectric.com/fa/shop/material-page/000000000000717286>

#### FA-COM PLC: Main Unit

Series	MELSEC IQ-F SERIES
Type	FX5S
Power Supply (V)	24
Current Type	DC
Program Memory	48K STEPS
Program Memory Unit	FLASH
Integrated Digital Inputs	36
Integrated Digital Outputs	24
Output Type	TRANSISTOR
Output Logic	SOURCE
Local I/O Points	60
Local + Remote I/O Points	256
Expandable	NO
Cycle Time LD (ns)	84
Cycle Time MOV (ns)	100
USB	1
Ethernet Port	1
Power Consumption (W)	16
Protection Class	IP10
Min. Ambient Temperature (°C)	-20
Max. Ambient Temperature (°C)	55

#### Logistic Dimensions & Gross Weight

Length (cm)	23,0
Width (cm)	15,0
Height (cm)	11,0
Gross Weight (kg)	0,700
Volume (cdm)	5,100

#### Stock Data

Planned Delivery Time (Days)	77
------------------------------	----

#### Life Cycle

Sales Start	28.06.2024
Predecessor	<a href="#">231481 / FX3G-60MT/DSS</a>

#### Additional Product Information

Battery included	NO
------------------	----

#### Export Data

Commodity Code	85371091
Legal Control (Dual Use List)	Not Listed
Country of Origin	Japan (JP)
Preference Status (Supplier Declaration)	Non EU

## Environmental

REACH Limit Exceeded	NO
Dangerous Goods Class	NO
Dangerous Goods Identifier	NO
RoHS Compliance	COMPLIANT
WEEE	B2B

## Conformity

CE	COMPLIANT
EAC	NON-COMPLIANT

## Documentation & Media Data

Manual URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=bltdae25c2bd5f2ff94&amp;q=FX5S-60MT/DSS&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=bltdae25c2bd5f2ff94&amp;q=FX5S-60MT/DSS&amp;doc-lang=en</a>
Certificates URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt8050dd1408c11cc2&amp;q=FX5S-60MT/DSS&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt8050dd1408c11cc2&amp;q=FX5S-60MT/DSS&amp;doc-lang=en</a>
CAD URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt26ecc97a31a841c1&amp;q=FX5S-60MT/DSS&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt26ecc97a31a841c1&amp;q=FX5S-60MT/DSS&amp;doc-lang=en</a>

## Product Packaging

Cardboard (g)	147
Other paper (g)	3,35
Aluminum (g)	0
Steel (g)	0
Styrofoam (g)	0
Other plastic (g)	0
Wood (g)	0
Glass (g)	0
Others (g)	0

## Compatible products

Material	Description / Price List Text / Classification
<a href="#">697551</a>	IE-C6A-0.2m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.2m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697582</a>	IE-C6A-0.5m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.5m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697583</a>	IE-C6A-1.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 1.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697584</a>	IE-C6A-2.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 2.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697585</a>	IE-C6A-5.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 5.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697586</a>	IE-C6A-10.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 10.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697587</a>	IE-C6A-15.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 15.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697588</a>	IE-C6A-20.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 20.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697589</a>	IE-C6A-25.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 25.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697590</a>	IE-CB-1piece CC-Link Bending tool for Patch Cable, RJ45, 1 piece, 90°Deg radius Class 100100215: FA-MOD PLC: Other Option
<a href="#">697591</a>	IE-C6A-CON-1pc CC-Link IE Certified Patch Cable connector, easy clip, RJ45, Cat.6A, 1pc Class 100100215: FA-MOD PLC: Other Option
<a href="#">717285</a>	EDS-G2008-EL 8Port Entry-level Unmanaged Switch,10/100/1000BaseT(X),CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module
<a href="#">717286</a>	EDS-G2005-EL 5Port Entry-level Unmanaged Switch,10/100/1000BaseT(X),CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module