

MECCA PRO TC-6T TT MECHANICS TOOL KIT 37 PIECES



- Includes pliers, torque screwdriver, socket set 3/8" drive and screwdrivers
- Insulated tools for live working up to 1,000 volts
- Integrated protective insulation with two colours to clearly indicate if there is any damage
- All tools are laid in individual TT modules, easy to see if any tool is missing
- Supplied in the unique TengTools service case with the tools supplied in 6 TengTools TT modules
- Nonslip rubber feet to prevent the case from sliding and which protects against scratching
- Secure lock system with click mechanism so you know the top is closed properly
- Hard wearing hinge with metal pin for increased life
- Retractable handle design for comfort and durability

Tool Kit TC-6T Mechanics Service Kit 37 Piece

General information

Country of origin: Taiwan
Barcode: 5020385011564
Tarriff code Europe: 8206000000
ECCN US: EAR99
ETIM: EC000149
UNSPSC: 27113201

Dimensions

Net weight (g): 97400
Width (mm): 468
Depth (mm): 350
Height (mm): 130

Attributes

Product type: Portable Tool Kits
Certificates: N/A
Number of pieces: 37
Insulated: Yes
Inlay material: PS
Colour: Red

Features



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 01-08-2024 19:59



Sandbergsvägen 3
 441 39 Alingsås, Sweden

ADDITIONAL IMAGES



WWW.TENGOOLS.COM





LIST OF CONTENTS



TC-6T02 MECCA PRO TC-6T TT Mechanics Tool Kit 37 Pieces

TC-6T	MECCA PRO TC-6 Carrying Case
TT04	Storage Tray TT1 6 Compartments
TTDV910N	Insulated Screwdriver Set Mixed TT2 10 Pieces
MDV820N	Flat Insulated Screwdriver 0.4 × 2.5 mm
MDV822N	Flat Insulated Screwdriver 0.5 × 3.0 mm
MDV824N	Flat Insulated Screwdriver 0.8 × 4.0 mm
MDV826N	Flat Insulated Screwdriver 1.0 × 5.5 mm
MDV840N	PH Insulated Screwdriver PH0
MDV842N	PH Insulated Screwdriver PH1
MDV844N	PH Insulated Screwdriver PH2
MDV860N	PZ Insulated Screwdriver PZ0
MDV862N	PZ Insulated Screwdriver PZ1
MDV864N	PZ Insulated Screwdriver PZ2

TTV3814 3/8" Insulated Socket Set TT1 14 Pieces

MV3800	3/8" Insulated Ratchet 72 Teeth
MV380020	3/8" Insulated Extension Bar 75 mm
MV380508	3/8" Insulated Socket 8 mm
MV380509	3/8" Insulated Socket 9 mm
MV380510	3/8" Insulated Socket 10 mm
MV380511	3/8" Insulated Socket 11 mm
MV380512	3/8" Insulated Socket 12 mm
MV380513	3/8" Insulated Socket 13 mm
MV380514	3/8" Insulated Socket 14 mm
MV380515	3/8" Insulated Socket 15 mm
MV380516	3/8" Insulated Socket 16 mm
MV380517	3/8" Insulated Socket 17 mm
MV380518	3/8" Insulated Socket 18 mm
MV380519	3/8" Insulated Socket 19 mm

TTV440 Insulated Plier Set TT1 4 Pieces

MBV441-6	Insulated Side Cutting Plier 160 mm
MBV451-7	Insulated Combination Plier 185 mm
MBV461-8	Insulated Long Nose Plier 215 mm
MBV499-7	Insulated Wire Stripping Plier

TTVSD09 Insulated Torque Screwdriver Set TT1 9 Pieces

1492TVSD	Insulated Torque Screwdriver 1-5Nm
MDV731	Interchangeable Blade Insulated Screwdriver 3 mm
MDV732	Interchangeable Blade Insulated Screwdriver 4 mm
MDV733	Interchangeable Blade Insulated Screwdriver 5.5 mm
MDV734	Interchangeable Blade Insulated Screwdriver 6.5 mm

- MDV751** Interchangeable Blade Insulated Screwdriver PH1
- MDV752** Interchangeable Blade Insulated Screwdriver PH2
- MDV771** Interchangeable Blade Insulated Screwdriver PZ1
- MDV772** Interchangeable Blade Insulated Screwdriver PZ2