

FEATURES

- Strong
- Heavy duty with reinforced base, sides and stacking rim
- Resistant to most industrial solvents
- Hygienic, clean, smooth inside faces guard against build-up of grease etc
- Available in 7 sizes and 6 colours as standard
- Index card slot for instant product identification

RS PRO PP Storage Bin Storage Bin, 130mm x 205mm, Orange

RS Stock No.: 469-6762



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro range of high-quality plastic storage bins made from robust polypropylene designed for simple and effective small parts organisation and storage in the workplace and in the home. These storage bins are stackable and can be stacked on top of one another to provide both a space saving solution to your storage needs and ease of handling

General Specifications

| | |
|--------------------|---|
| Material | PP |
| Colour | Orange |
| Size | Size 4 |
| Application | Home, Office ,Warehouse ,Laboratory ,Hospital, Garage |

Mechanical Specifications

| | |
|---------------------------------------|------------|
| Volume | 9.1 litres |
| Maximum Container Stack Height | 6mm |
| Maximum Stack Load Capacity | 36kg |
| Weight | 24kg |

| External dimensions | | |
|---------------------|-----------------------|-----------|
| Dimension | 350mm x 205mm x 130mm | |
| Depth | 350mm | (Overall) |
| Width | 205mm | (Overall) |
| Height | 130mm | (Overall) |
| Base Length | 300mm | (Overall) |


| Internal dimensions | |
|---------------------|-----------------------|
| Dimension | 330mm x 179mm x 117mm |
| Depth | 330mm |
| Width | 179mm |
| Height | 117mm |
| Base Length | 287mm |

Operation Environment Specifications

| | |
|-----------------------------|----------------|
| Operating Temperature Range | -15°C to +50°C |
|-----------------------------|----------------|

Approvals

| | |
|---------------------------|-----------------------|
| Compliance/Certifications | BS IEC 61340-5-1:2007 |
|---------------------------|-----------------------|



| All Dimensions in mm | SIZE 1 | SIZE 2 | SIZE 3 | SIZE 4 | SIZE 5 | SIZE 6 | SIZE 7 |
|--|---------------|---------------|---------------|---------------|---------------|---------------|---------------|
| (A) Overall Length | 90 | 167 | 240 | 350 | 350 | 376 | 510 |
| (B) Overall Width | 100 | 101 | 150 | 205 | 205 | 419 | 315 |
| (C) Overall Height | 50 | 76 | 130 | 130 | 181 | 180 | 200 |
| (D) Overall Base Length | 64 | 143 | 200 | 300 | 300 | 310 | 450 |
| (A) Internal Length | 80 | 154 | 223 | 330 | 330 | 350 | 470 |
| (B) Internal Width | 88 | 88 | 128 | 179 | 177 | 378 | 270 |
| (C) Internal Height | 42 | 63 | 120 | 117 | 167 | 164 | 188 |
| (D) Internal Base Length | 65 | 131 | 188 | 287 | 287 | 295 | 435 |
| Volumes (Litres) | 0.46 | 1.27 | 4.6 | 9.1 | 12.8 | 28.3 | 31.4 |
| Maximum Container Stack Height – (See Details Opposite) | 7 | 5 | 4 | 6 | 4 | 8 | 6 |
| Maximum Stack Load Capacity (kg) | 12 | 12 | 30 | 36 | 45 | 60 | 42 |

| Description | H x W x D (mm) | RS Stock Code / Colour | | | | | | | |
|----------------------------|-----------------|------------------------|----------|----------|----------|----------|----------|----------------|---------------|
| | | White | Blue | Red | Green | Yellow | Orange | Black Recycled | ESD Black |
| Size 1 | 50 x 100 x 90 | 315-1123 | 484-3996 | 484-3974 | 484-3980 | 484-3823 | 469-6728 | 909-6902 | 550-319 |
| Size 2 | 75 x 100 x 165 | 315-1139 | 484-4028 | 484-4006 | 484-4012 | 484-3839 | 469-6784 | 909-6906 | 550-325 |
| Size 3 | 132 x 150 x 240 | 315-1145 | 484-4056 | 484-4034 | 484-4040 | 484-4062 | 469-6778 | 909-6915 | 550-331 |
| Size 4 | 132 x 205 x 350 | 315-1151 | 484-4107 | 484-4078 | 484-4090 | 484-4113 | 469-6762 | 909-6918 | 909-6928 |
| Size 5 | 182 x 205 x 350 | 315-1173 | 484-4157 | 484-4129 | 484-4135 | 484-4163 | 469-6756 | 909-6912 | 909-6937 |
| Size 6 | 182 x 420 x 375 | 315-1189 | 484-4185 | 484-3845 | 484-4179 | 484-4191 | 469-6740 | 909-6921 | 909-6930 |
| Size 7 | 200 x 310 x 520 | 456-3426 | 350-5873 | 350-5845 | 350-5895 | 350-5867 | 469-5157 | 909-6924 | Not Available |
| Clear Bin Front for Size 7 | | 456-3432 | | | | | | | |

