

# THERMOMARK-RIBBON 110/50 - Ink ribbon



0800687

<https://www.phoenixcontact.com/gb/products/0800687>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black

## Commercial data

Item number	0800687
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG1223
Product key	BG1223
Catalog page	Page 144 (C-3-2019)
GTIN	4046356644822
Weight per piece (including packing)	114 g
Weight per piece (excluding packing)	111.6 g
Customs tariff number	96121010
Country of origin	CN

# THERMOMARK-RIBBON 110/50 - Ink ribbon



0800687

<https://www.phoenixcontact.com/gb/products/0800687>

## Technical data

### Product properties

Product type	Ink ribbon
--------------	------------

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Dimensions

Width	110 mm
Length	50 m
Length of roll	50 m

### Material specifications

Color	black (RAL 9005)
Material	Polyester

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Permissible humidity (operation)	30 % ... 85 %
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months after production date.

# THERMOMARK-RIBBON 110/50 - Ink ribbon



0800687

<https://www.phoenixcontact.com/gb/products/0800687>

## Classifications

### ECLASS

ECLASS-13.0	19140614
-------------	----------

### ETIM

ETIM 9.0	EC001694
----------	----------

### UNSPSC

UNSPSC 21.0	44103100
-------------	----------

# THERMOMARK-RIBBON 110/50 - Ink ribbon



0800687

<https://www.phoenixcontact.com/gb/products/0800687>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)