

Features

- Keeps essential electrical isolation devices within arm's reach of machinery.
- Shadows indicate missing or in-use devices, improving visual management and accountability.
- Built with 4mm Aluminium Composite Panel for long-lasting industrial use.
- **Complete with Hardware** – Mounting components included for quick and secure installation.
- **Fully Equipped with LOTO Devices** – Comes pre-stocked with lockout goods for immediate implementation of isolation procedures.

RS PRO Shadow Lockout Station - Electrical (With Devices)

RS Stock No.: 0694387



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Buy this product from www.rspro.com

- *The Shadow Lockout Station is a purpose-built, wall-mounted LOTO board designed to centralise electrical isolation devices near machines.*
- *Shadows on the board act as visual placeholders, instantly indicating which lockout tools are in use or missing.*
- *Made from durable 4 mm ACP sheets, ensuring strength and longevity even in harsh industrial settings.*
- *The station promotes better organization, faster response times, and reduced downtime during lockout procedures.*
- *Supplied with mounting hardware and equipped with electrical lockout devices, making it a ready-to-deploy solution for electrical safety compliance.*
- *Ideal for manufacturing units, maintenance departments, and electrical workshops needing streamlined LOTO implementation.*

General Specifications

Type	Shadow Lockout Station
Material	4mm ACP boards
Colour	Red & White
Package	BOPP + Box

Mechanical Specifications

Dimensions	1181mm x 1194mm
Width	1181mm
Height	1194mm
Weight	11.92 Kgs

Operation Environment Specifications

Withstand temperature	-20 °C to +80 °C
-----------------------	------------------

Station Components:

Item Name	Item Description	Quantity
Lockout Hasp	Vinyl Coated Hasp - Small	1
Lockout Hasp	Vinyl Coated Hasp - Premier	1

Lockout Hasp	Di-Electric Slider Hasp for 4 Locks / 3 mm shackle	1
Lockout Hasp	Di-Electric Slider Hasp for 4 Locks / 6 mm shackle	1
Lockout Hasp	Di-Electric Hasp 3 holes / 3 mm shackle	1
Lockout Hasp	Di-Electric Hasp 3 holes / 6 mm shackle	1
Lockout Hasp	Di-electric Lockout Hasp (6 Holes)	1
Lockout Hasp	Di Electric Hasp 6 holes / 6 mm shackle	1
Lockout Padlock	Lockout Padlock with Unique Key	10
Circuit Breaker Lockout	Miniature Circuit Breaker Lockout Pin In Standard	2
Circuit Breaker Lockout	Miniature Circuit Breaker Lockout Pin Out Standard	2
Circuit Breaker Lockout	Miniature Circuit Breaker Lockout Pin Out Wide	2
Circuit Breaker Lockout	Tie Bar - MCB Lockout	1
Circuit Breaker Lockout	Universal Circuit Breaker Lockout - Red with Twister Screw	1
Circuit Breaker Lockout	Universal Multi - Functional Circuit Breaker Lockout	1
Circuit Breaker Lockout	Universal Golden Toggle - Miniature Circuit Breaker Lockout	2
Circuit Breaker Lockout	Two Way Black MG Toggle Hasp	2
Circuit Breaker Lockout	Universal Multi Pole Breaker Lockout Device	1
Circuit Breaker Lockout	Tool Free Universal Circuit Breaker Lockout Device	2
Circuit Breaker Lockout	Clamp on Breaker Lockout - Small with Cleat	2
Circuit Breaker Lockout	COBL - Medium for 480 / 600 V breakers with Cleat	1
Circuit Breaker Lockout	COBL-Large fits on breaker switches up to 21/4" wide and 7/8" thick	1
Circuit Breaker Lockout	Large Circuit Breaker Lockout Round Handle	1
Mushroom Lockout	Normal Push Button Lockout	1
Cocoon Lockout	Oversize Push Button Lockout – Cocoon	1
Socket Lockout	Pin & Sleeve Socket Lockout – Small	1
Socket Lockout	Pin & Sleeve Socket Lockout – Medium	1
Socket Lockout	Pin & Sleeve Socket Lockout – Large	1
Plug Lockout	Pin & Sleeve Plug Lockout	2
Plug Lockout	Small Plug Lockout – Premier	1
Plug Lockout	Large Plug Lockout – Premier	1
Cord Lockout	Computer Power Cord Lockout	1
Fuse Lockout	Universal Fuse Holder Lockout – Red	1
Fuse Lockout	Universal Fuse Holder Lockout – Slim	1
Fuse Lockout	Fuse Holder Lockout – Thin Grip Type	1
Fuse Lockout	Fuse Holder Lockout – Wide Grip Type	1
Fuse Lockout	Safe Grip Fuse Puller	1
Multipurpose Cable Lockout	Economy Multipurpose Cable Lockout with 2 Mtrs. Vinyl Coated Steel Cable Without loop	1
Multipurpose Cable Lockout	Squeezer Multipurpose Cable Lockout - Di-electric	1
Lockout Sign	Hanging Lockout Sign (8 x 6 inch)	1
Lockout Tags	"Do Not Operate" Lockout Safety Tags	20
Lockout Ties	10" Nylon Ties	20
Lockout Pen	Black Marker Pen	1
Screw Driver	Industrial Grade Flat Screwdriver	1

Circuit Breaker Lockout	Universal Large Circuit Breaker Lockout	1
Circuit Breaker Lockout	Miniature Circuit Breaker Lockout – Yellow	1
Circuit Breaker Lockout	MCB Lockout – Green Siemens	1
Circuit Breaker Lockout	Schneider Circuit Breaker Lockout – Yellow	1
Group Lockout Box	Group Lockout Box – Red 7	1
Panel Lockout	Electrical Panel Handle Lockout	1
Fuse Lockout	Lockout Insulation Plugs for Bottle Fuses for E14 or E18	1
Fuse Lockout	Lockout Insulation Plugs for Bottle Fuses for E27 or E33	1
Fuse Lockout	Universal Fuse Carrier Isolation Lock	1
Plug Lockout	Electrical Multi Plug Lockout	1
Circuit Breaker Lockout	Motor Protection Circuit Breaker Lockout Device	1
Shadow Lockout Station	Shadow Lockout Station – Electrical	1