



SIVACON, door, left, ventilated, IP20, H: 2000 mm, W: 450 mm, RAL 7035, protection class 1

| Model                               |  |                           |       |
|-------------------------------------|--|---------------------------|-------|
| product brand name                  |  | SIVACON                   |       |
| product designation                 |  | Door                      |       |
| design of the product               |  | With ventilation openings |       |
| design of the surface               |  | Powder-coated             |       |
| design of the product EMC version   |  | No                        |       |
| Protection class                    |  |                           |       |
| protection class IP                 |  | IP20                      |       |
| operating resource protection class |  | safety class 1            |       |
| Appearance                          |  |                           |       |
| RAL color number                    |  | 7035                      |       |
| color                               |  | light grey                |       |
| Product details                     |  |                           |       |
| product component                   |  |                           |       |
| • ventilation                       |  | Yes                       |       |
| • viewing door                      |  | No                        |       |
| • door for disconnecter lock        |  | No                        |       |
| Mechanical Design                   |  |                           |       |
| height                              |  | 2 000 mm                  |       |
| width                               |  | 450 mm                    |       |
| opening direction of the door       |  | left                      |       |
| net weight                          |  | 15 kg                     |       |
| material                            |  | steel                     |       |
| Approvals Certificates              |  |                           |       |
| General Product Approval            |  | Test Certificates         | other |



[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

|       |             |
|-------|-------------|
| other | Environment |
|-------|-------------|

[Miscellaneous](#)



[Environmental Confirmations](#)

| Further information          |
|------------------------------|
| Information on the packaging |

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1070-2UT15-1BA2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1070-2UT15-1BA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1070-2UT15-1BA2](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1070-2UT15-1BA2)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/13/2025 

