


Plastic enclosures, assembled stations 1, 2 & 3 seat, 22mm Modular Range

1-seat Plastic enclosures. Yellow top/light grey bottom




Description					Catalog No.
	Pos - 1	Pos - 2	Pos - 3	Pos - 4	
Type	Twist Release 40mm E	—	—	—	P1-ES
	Stop	—	—	—	
Color	Red	—	—	—	
Contacts	2 NC	—	—	—	
Name plate	EMERGENCY STOP	—	—	—	
Type	Ill. Twist Release 40mm E	—	—	—	P1-1ES
	40mm E-Stop	—	—	—	
Color	Red, 120V filament	—	—	—	
Contacts	2 NC, 1 LB	—	—	—	
Name plate	EMERGENCY STOP	—	—	—	

1-seat Plastic enclosure, dark grey top/light grey bottom


Description					Catalog No.
	Pos - 1	Pos - 2	Pos - 3	Pos - 4	
Type	3-pos sel. Main	—	—	—	P1-HOA
Color	Black	—	—	—	
Contacts	2 NO	—	—	—	
Name plate	HAND/OFF/AUTO	—	—	—	

2-seat Plastic enclosure, dark grey top/light grey bottom



Description					Catalog No.
	Pos - 1	Pos - 2	Pos - 3	Pos - 4	
Type	Button mom, Ext.	Button mom, Flush	—	—	P2-SS
Color	Red	Green	—	—	
Contacts	1 NC	1 NO	—	—	
Name plate	STOP	START	—	—	
Type	3-pos sel. Main	Pilot Light	—	—	P2-1HOARL
Color	Black	Red	—	—	
Contacts	2 NO	1 LB, 120V filament	—	—	
Name plate	HAND/OFF/AUTO	RUN	—	—	
Type	2-pos sel. Main	Pilot Light	—	—	P2-100RL
Color	Black	Red	—	—	
Contacts	1 NO	1 LB, 120V filament	—	—	
Name plate	ON/OFF	RUN	—	—	

3-seat Plastic enclosure, dark grey top/light grey bottom



Description					Catalog No.
	Pos - 1	Pos - 2	Pos - 3	Pos - 4	
Type	Button mom, Ext.	Button mom, Flush	Pilot Light	—	P3-1SSRL
Color	Red	Green	Red	—	
Contacts	1 NC	1 NO	1 LB, 120V filament	—	
Name plate	STOP	START	RUN	—	
Type	3-pos sel. Main	Pilot Light	Pilot Light	—	P3-1HOARLGL
Color	Black	Red	Green	—	
Contacts	2 NO	1 LB, 120V filament	1 LB, 120V filament	—	
Name plate	HAND/OFF/AUTO	RUN	OFF	—	
Type	2-pos sel. Main	Pilot Light	Pilot Light	—	P3-100RLGL
Color	Black	Red	Green	—	
Contacts	1 NO	1 LB, 120V filament	1 LB, 120V filament	—	
Name plate	ON/OFF	RUN	OFF	—	
Type	3-pos sel. Main	Button mom, Flush	Pilot Light	—	P3-1HOASRL
Color	Black	Green	Red	—	
Contacts	2 NO	1 NO	1 LB, 120V filament	—	
Name plate	HAND/OFF/AUTO	START	RUN	—	
Type	Twist Release 40mm E Stop	3-pos sel. Main	Pilot Light	—	P3-1ESHOARL
Color	Red	Black	Red	—	
Contacts	2 NC	2 NO	1 LB, 120V filament	—	
Name plate	EMERGENCY STOP	HAND/OFF/AUTO	RUN	—	
Type	5kOhm Pot	Stop	Start	—	MEP3-SSPOT5
Color	Black	Red	Green	—	
Contacts	Leads	1NO+1NC	1NO+1NC	—	
Name Plate	Scale	(text cap)	(text cap)	—	