



1630

Protector

Transport Case

Sensitive equipment needs protection, and since 1976 the answer has been the Peli™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Peli cases have survived.

Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **4 strong polyurethane wheels with stainless steel bearings (wheel diameter is 5.3cm)**
- **Watertight, crushproof, and dustproof**
- 3 level Pick N Pluck™ with convoluted lid foam
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Easy open double-throw latches
- Fold down handles
- Note: Please consult a sales specialist for more details.
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Reinforced corners
- Retractable extension trolley handle
- Stackable
- Stainless steel padlock protectors
- Peli's legendary lifetime guarantee**
- * Where applicable by law



CONFIGURATIONS



1630
Standard



1634
With Padded Dividers



1630NF
No Foam



1630WF
With Foam

DIMENSIONS

Interior (LxWxD)	27.70 x 20.98" x 15.50 (70.4 x 53.3 x 39.4 cm)
Exterior (LxWxD)	31.28 x 24.21" x 17.48 (79.5 x 61.5 x 44.4 cm)
Lid Depth	3.25" (8.3 cm)
Bottom Depth	12.14" (30.8 cm)
Total Depth	15.39" (39.1 cm)
Int Volume	5.21 ft³ (0.148 m³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Polypropylene
-------------	---------------

Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Desert Tan	 OD Green
---	--	--

WEIGHT

Weight With Foam	36.00 lbs (16.33 kg)
Weight Empty	31.00 lbs (14.06 kg)
Buoyancy	350.00 lbs (158.76 kg)
Master Pack Weight	42.00 lbs (19.05 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	190°F (87.8 °C)

CERTIFICATIONS

IP67
Def Stan 81-41

OTHER

Wheels	4
Extendable Handle	yes
Master Pack	1
Nameplate	yes
Reduced Area	yes

ACCESSORIES



1631
5 pc. Replacement Foam Set



1633
Replacement O-ring



1635
Padded Divider Set



1639
Lid Organizer



1630DC
Document Container
Accessory



1507QM
Quick Mounts - set of 4



1506TSA
TSA Lock



1500D
Desiccant Silica Gel

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 08-19-26