

NEW Product



WEATHERSAFE IP66 RATING

TGV204N

Passive GREY BUTTON

TGV204N

Weathersafe Vision Twin Gang 13A Switched RCD Socket – Passive

Weathersafe Vision Switched RCD Socket gives additional protection against the risk of electric shocks at home and in the garden. Ideal for use with lawnmowers, hedge trimmers etc.

- Weathersafe 'Vision' see-through clear plastic cover.
- Extra fast action – trips out within 40 milliseconds (BS7288).
- Contacts remain latched when power supply is temporarily lost.
- Impact resistant housing.
- Easy release lid catch.
- Multiple M20 threaded screw-outs.
- Test and reset buttons for safety checks.
- Status flag indicator.
- Spacious design allowing full closure of lid with plug in position.
- Suitable for all 13 amp BS plugs.
- Complies with BS7288 and BS1363.
- IP66 weatherproof rating.

NEW Product



WEATHERSAFE IP66 RATING

TGV205N

Active BLUE BUTTON

TGV205N

Weathersafe Vision Twin Gang 13A Switched RCD Socket – Active

Shares all the features of the TGV204N but contacts break when power supply is temporarily lost.

- Weathersafe 'Vision' see-through clear plastic cover.
- Extra fast action – trips out within 40 milliseconds (BS7288).
- Automatically disconnects both Live and Neutral connections leaving Earth connection intact.
- Trips out when the power supply is temporarily lost. A safety must for machine tool applications.
- Impact resistant housing.
- Easy release lid catch.
- Multiple M20 threaded screw-outs.
- Test and reset buttons for safety checks.
- Status flag indicator.
- Spacious design allowing full closure of lid with plug in position.
- Suitable for all 13 amp BS plugs.
- Complies with BS7288 and BS1363.
- IP66 weatherproof rating.



WEATHERSAFE IP66 RATING

TGVL01/TGVL03/TGVL05

TGVL01

Weathersafe Single Gang 2-Way Switch (SP)

- 10AX (fluorescent rated).
- Backlit neon illuminates switch for dark areas.
- Complies with BSEN60669.
- Multiple 20mm knock outs.
- IP66 weatherproof rating.

TGVL03

Weathersafe Single Gang Bell Push Switch (SP)

- 10AX (fluorescent rated).



WEATHERSAFE IP66 RATING

TGVL02

TGVL02

Weathersafe Twin Gang 2-Way Switch (SP)

- 10AX (fluorescent rated).
- Backlit neon illuminates switch for dark areas.
- Complies with BSEN60669.
- Multiple 20mm knock outs.
- IP66 weatherproof rating.

TGVL05

Weathersafe Single Gang 2-Way Switch (DP)

- 20AX (fluorescent rated).

3 YEAR GUARANTEE INCLUDED

All these products carry a 3 year guarantee.



See pages 93 & 94 for product specifications.



There is simply no more need to trail an outdoor cable through to an indoor socket, leaving a door or window open.

When using various garden equipment it is just a simple matter of opening the lid, unplugging one piece of equipment and replacing it with another – use the double gang versions and you don't even need to do that.

Remember... there's no more need for that indoor lead!



Weathersafe
VISION

Weathersafe Vision will accommodate all UK plugs with the lid closing fully. This totally encloses and protects the plugs.

The added bonus of a lockable lid safeguards against unauthorised opening and tampering.

