



Main

Product brand	Schneider Electric
Range	New Unica
Aesthetic name	New Unica
Product or component type	Connected switch
Concentrator compatibility	Wiser hub generation 2
Mobile App name	Wiser Home

Complementary

Device presentation	Mechanism with fixing frame
Technology type	Electronic
Number of rocker	2
Actuator	Push-button
[Ue] rated operational voltage	3 V DC 2.4 GHz
Colour tint	Aluminium
Surface finish	Matt
Surface treatment	Painted
Number of modules	2 modules
Number of FUNCTION keys	1 2
Local signalling	Commissioning: 1 1 LED per channel (green/red)
Signalling function	Commissioning
Number of outputs	1 remote control 2 remote control
Control type	Push-button wiring device adaptation push-button
Software name	Wiser App: device setup
Time delay	Without time delay
Maximum number of connected devices	Zigbee 3.0: 10 free (0-50 °C)
Technology type	Zigbee 0-50 °C
Communication network type	Wireless (2.4 GHz), 2.5 mW at < 50 m
System requirements	Android 5.1 or higher Wiser Home control
Connected auxiliaries	Up to 11 wired devices, distance : < 50 m
Marking	-
Provided equipment	Adhesive tape
Material	PC (polycarbonate) GF10 FR: LED

Mounting support	Backplate
Device mounting	Direct mounting
Fixing mode	By 2 screws
Type of installation	Indoor
Quantity per set	Set of 1
Type of packing	Box
Embedding depth	0 Mm
Depth	12 Mm
Width	74.5 Mm
Height	74.5 Mm
Net weight	0.025 Kg
Resistance to chemical agents	Resistant to alcohol (70 %)

Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...45 °C
IP degree of protection	IP20 0-50 °C
Relative humidity	5...95 % 0-50 °C
IK degree of protection	IK03
Environmental characteristic	Indoor use
Environmental health and issues	Lead free
Directives	2014/35/EU - low voltage directive
Product certifications	CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.7 Cm
Package 1 Width	9.5 Cm
Package 1 Length	9.5 Cm
Package 1 Weight	88 G
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	30 Cm
Package 2 Width	30 Cm
Package 2 Length	40 Cm
Package 2 Weight	3.665 Kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and neve
Take-back	No
Removable battery	User replaceable