



Impact



Heavy Duty

Robust impact-resistant gloves, granting high cut and abrasion resistance with a firm grip

- **Advanced defenses:** EDGE[®] 48-205 cut protection gloves feature a palm made from high-performance fibers that meet ANSI A6 cut resistance standard
- **Specialized protection:** Made for heavy-duty extraction and maintenance work, these protective gloves possess back-of-hand PVC bumpers that significantly reduce the risk of crush, pinch and impact injuries
- **Enhanced grip:** EDGE[®] 48-205 industrial gloves afford a reliable grip thanks to the unique material used on the palm
- **Optimized visibility:** These bright yellow cut-resistant gloves ensure that hands are visible and safe in dark conditions
- **Added features:** Reinforcement patches extend the wear life of EDGE[®] 48-205 hand protection gloves, while their wide neoprene cuff allows easy donning and doffing



Industries

- Machinery and Equipment
- Oil and gas
- Maintenance
- Mining

Applications

- Drilling / Extraction
- Exploration
- Heavy-duty Maintenance
- Production/Processing
- Roughneck & Roust about tasks

Key Features

- **High cut resistance palm:** Advanced laceration defenses
- **Back-of-hand protection:** For safety gloves with added hand protection
- **Excellent grip:** Secure handling in dry, wet and oily environments

Performance Standards & Regulatory Compliance

ANSI/ISEA 138-2019



ANSI 138

ANSI/ISEA 105-2024



EN388: 2016



4X44FP

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE® 48-205	Finishing: Vinyl TPR Bumper Liner Material: Aramid, Fiber glass, Polyester, Nylon Cuff Style: Safety Cuff	N/A	8, 9, 10, 11, 12	250 to 280 mm, 9.84-11.02 Inches	Black	1 pair/pack, 6 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699